

Model 800 1", N.m/lbf.ft



These Wrenches were designed as an extension to our 'Professional' range of Torque Wrenches, Models 60 - 330 and so have the same high quality and accuracy.

Part number: 14016

EAN Bar Code: -

NATO number: -

Accuracy: +/- 3%

Operates between:

150.0 - 600.0 lbf-ft

200.0 - 800.0 N·m

Model 800



TECHNICAL SPECIFICATIONS

- Length: 1035 mm
- Square Size: 1"
- Torque Radius: 883 mm
- Weight: 5.2 Kg
- Ratchet Teeth: 60
- Ratchet Type: push-through
- Length (inc. Ext. Handle): 1535 mm

FEATURES

- Accuracy of +/-3% of reading.
- Non length dependent. Extension handle can be used to reduce operator effort (handle supplied as standard with Model 800, 1000 and 1500).
- Positive 'click' can be heard seen and felt.
- Long scale length in N·m and lbf·ft allows error free setting.
- Fine 60 tooth ratchet allows the wrench to be used in confined areas.
- Supplied in a high quality blow moulded plastic case, with space provided for accessories such as sockets.