



mecalectro

Industrial Solenoid – Z.8.15D.AB.83



Stroke: 15 mm

Force at beginning of stroke (FM: 100/25/5%):
4/12/37 N

Force at end of stroke (FM: 100/25/5%):
13/45/100 N

Power Consumption: (FM: 100/25/5%):
16/58.5/275 W

Total mass: 400 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 230Vac

Possibles supplies: From 24 to 230Vac

Duty Cycle: Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 93700

Examples of applications: Automation, blocking, composting, distribution, stamping, punching