

41867

# Washing Brush w/long handle, 415 mm, Hard, Orange



The long handle on this brush allows the operator to reach into parts of equipment that are hard to access. The angled hard bristle works well for scrubbing at a distance, e.g. cleaning machines, deep buckets, containers and tubs or anywhere that may require longer reach.

# Technical Data

Item Number	41867
Visible bristle length	36 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	700 Pcs
Quantity Per Layer (Pallet)	70 Pcs.
Box Length	435 mm
Box Width	205 mm
Box Height	180 mm
Length	415 mm
Width	71 mm
Height	75 mm
Gross Weight	0,274 kg
Net Weight	0,24 kg
Cubik metre	0,0022 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020418679
GTIN-14 Number (Box quantity)	15705020418676
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact