



Deckplate

Durable deckplate provides comfort and grip

- Hardwearing PVC soil resistant diamond pattern surface.
- Self-extinguishing top surface provides resilience to many industrial chemicals.
- Comfortable foam 'cushion' backing for fatigue relief.
- Available as Safety Deckplate with bright yellow borders.
- Supplied with ramped edges.



Technical Specification

Material:	Vinyl top surface with PVC foam backing (fusion bonded, not glued)
Surface Finish:	Diamond pattern
Product Height:	14mm
Roll Length:	18.3m
Operating Temperature:	0°C to +60°C
Resistant to Chemicals:	The upper surface of the PVC provides limited resistance to chemicals and oils
Environmental Resistance:	Suitable for dry indoor environments
Typical Applications:	Packing stations, assembly areas, production lines where regular turning occurs
Installation Method:	Loose lay
Cleaning Method:	Brush/Mop the top surface
Country of Origin:	China

Sizes	Black	Black/Yellow	Weight
0.6m x 0.9m	DP010609	SD010701	4.00 kg
0.6m x 18.3m	-	SD010706	71.92 kg
0.6m x per linear metre	-	SD010706C	3.93 kg
0.9m x 1.5m	DP010915	SD010702	8.86 kg
0.9m x 3m	DP010903	SD010703	17.71 kg
0.9m x 6m	DP010906	SD010704	35.42 kg
0.9m x 18.3m	DP010005	SD010707	108.00 kg
0.9m x per linear metre	DP010005C	SD010707C	8.00 kg
1.2m x 18.3m	DP010007	SD010708	166.00 kg
1.2m x per linear metre	DP010007C	SD010708C	9.00 kg
1.5m x 18.3m	DP010011	SD010709	178.00 kg
1.5m x per linear metre	DP010011C	SD010709C	9.70 kg