



ENGLISH

Datasheet

RS Pro Pro 150W High Bay

RS Stock No: 176-8521



This RS Pro 150W LED High Bay is ideal for industrial and commercial applications such as factories and warehouses.

It is a suitable replacement for 300W HID Fittings and comes with an integral Driver and flicker free technology.

It also comes supplied with a hanging hook and 2m of power flex.

Also available is a microwave sensor that discretely installs on the face of the fitting.



ENGLISH

Typical Properties

Material	Aluminium
Wattage	150 W
Beam Angle	90°
Lumen Output	16,500 Lm
Lumen Efficiency	110 Lm/W
Lamp Type	Fixed LED
Voltage	220-240 V AC / 50-60Hz
Colour Temperature	Cool White
CCT	4000K
IP Rating	IP65
IK Rating	IK08
Rated Life	30,000hrs

