



ENGLISH

Datasheet

RS Pro Pro 5ft 40W LED NCF 240V Grey

RS Stock No: 176-8551



This RS Pro 5ft 40W LED NCF comes in 4ft, 5ft and 6ft options. With a high lumen output they are ideal for industrial and commercial applications such as warehouses, car parks, arenas and wet areas. With an ultra durable Polycarbonate body and diffuser and aluminium tray they are extremely light and offer even light distribution. They come pre fitted with stainless steel 304 clips making them an ideal fitting for food preparation areas with an operating temperature range of -25 to +50°C.



ENGLISH

Typical Properties

Material	Aluminium + Polycarbonate
Wattage	40W
Lumen Output	4000Lm
Lumen Efficiency	100 Lm/W
Ra	>70
Beam Angle	120°
Voltage	100 – 277V AC / 50-60Hz
Length	5ft / 1500mm
CCT	6300K
Colour Temp	Daylight
IP Rating	IP65
IK Rating	IK08

