



DWST1-75668

Toughsystem DS450 mobile storage

Selling Proposition

- IP65 level seal for water and dust protection
- Padlock eye
- Wide gripping area for pushing and pulling
- Bi-material telescopic handle
- Side latches for modules stacking
- Special design of lid opening with a rotating handle, enables maximum storage volume with a non-detachable lid

Standard Equipment

- Toughsystem DS450 mobile storage

Warranty Specifications

- 1 Year Warranty

Specifications	
Width	480 mm
Depth	99 mm
Height	597 mm
Max Load	50 Kg
Nail Diameter Range	