



TOUGHBOOK CF-33 TABLET

WINDOWS 10 PRO 12" FULLY RUGGED TABLET

TOUGHBOOK CF-33 TABLET, the 12.0" fully rugged device with hot swappable twin batteries and highly configurable capabilities brings unrivalled flexibility and performance for mobile business computing. Thanks to the optional detachable keyboard, the TOUGHBOOK CF-33 TABLET offers the best of all worlds for mobile workers. Target industries for the device include field service workers, maintenance and service technicians in utilities and telecommunications, as well as government agencies, defence, the police and other emergency services.

- Intel® Core™ i5-7300U vPro™ processor
- Windows 10 Pro
- Next generation Dual-touch (with digitizer) display with 3:2 aspect ratio
- 12.0" QHD (2160 × 1440) anti-reflective high brightness outdoor display (up to 1200cd/m²)
- Capacitive 10 finger multi-touchscreen with glove and rain modes
- Digitiser pen embedded in the tablet
- Optional detachable keyboard with various enterprise ports and backlit* keys
- Fully rugged design with water and dust resistance (IP65)**
- User exchangeable and hot-swappable twin batteries
- Up to 11 hours battery life with standard twin batteries (MobileMark™ 2014)
- Up to 22 hours battery life with extended* twin batteries (MobileMark™ 2014)
- Flexible configuration port*** and business expansion module***
- Optional vehicle mount

TOUGHBOOK





Yesterday's Legend, Today's Leader.

TOUGH YET VERSATILE

Panasonic TOUGHBOOK CF-33 TABLET is one of the first tablets powered by the latest 7th Generation Intel® Core™ i5-7300U vPro™ processor, delivering incredible performance, and is shipping with Windows 10 Pro. It also has a rich set of business interfaces with additional customisable options to meet a worker's needs. With its hot swappable twin batteries and outdoor viewing, glove-enabled touchscreen, it's a versatile yet tough technology companion for mobile workers.



Mobile Computing Platform	Intel® Core™ i5-7300U vPro™ processor 3 MB cache, 2.6 GHz up to 3.5 GHz with Intel® Turbo Boost Technology
Operating System	Windows 10 Pro
RAM & Storage	8GB RAM & 256 GB Solid State Drive (Serial ATA)
Graphic Chip	Intel® HD Graphics 620
LCD	12.0" QHD (2160 × 1440 pixels) anti-reflective sunlight-viewable IPS colour LCD (up to 1200cd/m ² brightness), 3:2 Aspect ratio
Touchscreen	Dual touch 10 finger capacitive multi-touchscreen with IP55 Digitiser as standard
Bluetooth®	Version 4.1 Class 1
WLAN	Intel® Dual Band Wireless-AC 8265
Mobile Broadband*	4G LTE (Sierra Wireless™ EM7305), Nano SIM in the tablet
Dedicated GPS*	U-blox NEO-M8N with GPS/GLONASS/SBAS Support
LAN	100BASE-T / 100BASE-TX / 10Base-T
Sound	WAVE and MIDI playback, Intel® High Definition Audio subsystem support, Microphone arrays (built-in)
Camera	Front: 2 MP Rear: 8 MP with autofocus and LED flash
Interface	USB 3.0: x1 USB 2.0: x1*** (configuration Port) LAN (Gigabit): x1 RJ-45 Serial port: x1 True serial*** (configuration Port) HDMI: x1 Headset: x1 Port replicator connector: x1 Dual external antenna connector: x1
Expansion slots	Micro SD/SDXC memory card: x1 micro SDXC
Project based options*	Tablet configuration port*** True serial port or 2D Barcode reader or 2nd USB 2.0 Tablet business expansion module*** Smartcard reader or Contactless smartcard reader or Fingerprint reader
Power	AC adapter: Input: 100 V - 240 V AC, 50 Hz/ 60 Hz, Output: 15.6 V DC, 4.06A Battery: Li-ion 11.1 V, 2x 1,990 mAh (Standard battery) Li-ion 10.8 V, 2x 4120 mAh (Extended battery*) Operating Time: 11 hours with standard twin batteries (MobileMark™ 2014) 22 hours with extended twin batteries* (MobileMark™ 2014)
Security Features	TPM (Trusted Platform Module, TCG V2.0 compliant), Integrated hardware security lock slot, Password security (supervisor password, user password, SSD lock)
Physical Dimensions (W x D x H)	With standard twin batteries (3+3 cell): 308.0 x 243.6 x 21.6mm {12.1" x 9.6" x 0.9"} With extended twin batteries (6+6 cell)*: 308.0 x 243.6 x 32.1mm {12.1" x 9.6" x 1.3"}
Weight	With standard twin batteries (3+3 cell): Approx. 1.527 kg {3.4 lb.} With extended twin batteries (6+6 cell)*: Approx. 1.882 kg {4.2 lb.}
Standard configuration	CF-33mk1, 8GB RAM, 256GB SSD, empty configuration port, standard twin batteries (3+3 cell)
Included in box	CF-33mk1 Tablet, twin 3 cell batteries, digitizer pen, tether and AC adapter
Accessories	AC Adapter CF-AA5713AE/G/T/D Desktop port replicator CF-VEB331U Standard battery pack (3 cell) CF-VZSU1AW Extended battery pack (6 cell) CF-VZSU1BW 4 bay battery charger CF-VCB331M Digitizer Stylus pen CF-VNP023U
Testing Standards	Water resistance test: IP-X5** Dust resistance test: IP-6X** Gravity drop resistance test: 150cm (5 feet)** Operating temperature: -29°C to +63°C {-20°F to 145°F}** Storage temperature: -51°C to +71°C {-60°F to 160°F}**

CF-33mk1: 23.05.2017

*Optional

** Tested by an independent third party lab following MIL-STD-810G and IEC 60529

***One option exclusively possible in configuration port / business expansion module

Intel, the Intel Logo, Intel Core, Intel vPro, Core Inside and vPro Inside are trademarks of Intel Corporation in the U.S. and other countries. Microsoft® and Windows® are registered trademarks of Microsoft® Corporation of the United States and/or other countries. All other brand names shown are the registered trademarks of the relevant companies. All rights reserved. All working conditions, times and figures quoted are optimum or ideal levels and may differ as a result of individual and local circumstances.

Computer Product Solutions (CPS) BU, Panasonic System Communications Company Europe (PSCUE), Panasonic Marketing Europe GmbH, Hagenauer Straße 43, 65203 Wiesbaden (Germany).

Panasonic

BUSINESS

www.toughbook.eu