

# TM40/12



TM40/12 Fail safe bell transformer



## General Information

Extended Product Type	TM40/12
Product ID	2CSM228775R0802
EAN	8012542287759
Catalog Description	TM40/12 Fail safe bell transformer
Long Description	These transformers, with safety extremely-low voltage secondary (SELV), are suitable for driving loads that call for a discontinuous supply.

## Ordering

EAN	8012542287759
Minimum Order Quantity	1 piece
Customs Tariff Number	85043121

## Dimensions

Product Net Width	0.054 m
Product Net Height	0.085 m
Product Net Depth / Length	0.065 m
Product Net Weight	0.450 kg

## Container Information

Package Level 1 Units	4 piece
Package Level 1 Width	0.09 m
Package Level 1 Height	0.08 m
Package Level 1 Depth / Length	0.054 m
Package Level 1 Gross Weight	1.8 kg
Package Level 1 EAN	8012542287766

## Additional Information

Options Provided	None
Power Supply	40 V·A
Product Main Type	TM
Product Name	Fail safe bell transformer
Secondary Voltage	4-8-12 V AC

---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CSC000001D0202
Declaration of Conformity - CE	2CSC446001D2702
Instructions and Manuals	On the product's body

---

## Classifications

ETIM 4	EC001547 - Bell transformer
ETIM 5	EC001547 - Bell transformer
ETIM 6	EC001547 - Bell transformer
Object Classification Code	T
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Command and Signalling devices → Bells and safety transformers

