



DEWALT 18V XR Grease Gun

DCGG571M1-GB



- 690 bar (10,000 PSI) output pressure with a flow rate of 147g per minute
- Delivers high pressure to clear clogged fittings
- Performs routine lubrication up to twice as fast as a manual grease gun
- Purge valve allows user to bleed excess air that can become trapped in pump valves
- 1m hose for hard-to-reach fittings
- Can be bulk-filled (suction or pump) or used with standard 400g grease cartridges
- LED light helps to illuminate fittings that are difficult to locate
- Pump filter screen on the unit helps to keep dirt from passing through the pump mechanism
- Includes shoulder strap for carrying the unit during applications

Description:

The DEWALT 18V XR Grease Gun has been designed to deliver up to 690 bar/10,000PSI of output pressure, helping to clear clogged fittings with high pressure. The grease gun performs routine lubrication more efficiently, up to twice the speed compared to a manual grease gun. The purge valve enables bleeding of excess air that can get trapped in pump valves affecting the pressure and speed of applications. A built in LED light has been integrated for enhanced visibility during applications and the anti-debris filter protects the pump mechanism from dirt and contamination. The unit can be bulk filled by either suction or pump or can be used with standard 400g grease cartridges.

Specifications	
Power	18 V
Battery Capacity	4.0 Ah
Output Pressure	690 Bar
Feed Rate	147.0 g/min
Grease Type	Up to NLGI #2