

## WIRE END CRIMPING PLIERS | 985895



### Description

- Stainless steel 5-cavity dies:
    - 0.5 to 0.75 mm<sup>2</sup>.
    - 1 to 1.5 mm<sup>2</sup>.
    - 2.5 mm<sup>2</sup>.
    - 4 mm<sup>2</sup>.
    - 6 mm<sup>2</sup>.
  - Unlocking accessible at all times.
  - Reversed crimping: terminal positioned on the fixed part for more effectiveness and precision.
  - Capacity 0.5 to 6 mm<sup>2</sup>.
  - Shape allowing hand setting.
  - Soft touch.
  - Length: 230 mm.
- Weight: 490 g.

### Information

I [mm]	230
L [mm]	230
[g]	490

