

LED, Base BA 15d, blue, 24 V AC/DC, accessory for signaling columns, with diameters 50 mm and 70 mm



Figure similar

General technical data	
Product brand name	SIRIUS
Product designation	LED
Type of voltage of the operating voltage	AC/DC
Operating voltage	
• 1 at DC rated value	24 V
• 1 at AC at 50 Hz rated value	24 V
• 1 at AC at 60 Hz rated value	24 V
Relative positive tolerance of the operating voltage	10 %
Relative negative tolerance of the operating voltage	-15 %
Consumed current maximum	15 mA
Color	blue
Reference code	
• acc. to DIN EN 61346-2	P
• acc. to DIN EN 81346-2	P
Mechanical data	
Outer diameter of the signal column element	70 mm

Lamp	
Type of light source	LED
Light intensity	0.21 cd
Mounting type	BA 15d

Ambient conditions	
Ambient temperature during operation	-20 ... +60 °C
Height	45 mm
Width	20 mm

Certificates/approvals			
General Product Approval	EMC	Declaration of Conformity	other



[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4428-6XF>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4428-6XF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD4428-6XF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4428-6XF&lang=en

last modified:

11/13/2018