



BE-02+ - USB RECHARGEABLE BEANIE LIGHT



Thinsulate: BE-02TH / **Black:** BE-02+
Orange: BE-02+O / **Yellow:** BE-02+Y

- 150 Lumen White Samsung® SMD LEDs
- 420mAh Lithium-polymer battery
- Gives between 2.5 and 6.5 hours of light from just one charge
- Light can easily be removed from the item of clothing and charged directly through a USB port
- Built-in USB charging connector
- Can be fully charged in 4 hours
- Press once to turn on and toggle between 3 light intensity levels. HIGH > LOW > 2 Hz FLASH > OFF

3M
Thinsulate
 INSULATION

USB
 CHARGING

SAMSUNG
 LED CHIP



CHARGE DIRECTLY FROM
 USB PORT - RED TO GREEN LIGHTS



SUPPLIED READY
 MERCHANDISED

150
 LUMEN
 OUTPUT

2½-6½
 HOURS
 RUNTIME

13
 METRE
 BEAM RANGE

IPX5
 WATER
 RESISTANCE

- High quality warm knitted beanie hat with integrated USB rechargeable LED light
- Comfortable knitted Beanie, one size fits all
- Material: 35% acrylic 65% polyester, machine washable at 30°C
- Thinsulate option also available
- Ideal for: Runners, Walkers, Camping, Plumbers, Electricians, Tradesman and Contract Engineers

BATTERY 3.7v 420 mAh Li-polymer Battery (inc.)

WEIGHT Light: 25g

DIMENSION Light: 74 x 41 x 15mm