

PushPull V4, compact housing vertical



Part number	09 45 545 0040
Specification	PushPull V4, compact housing vertical
HARTING eCatalogue	https://b2b.harting.com/09455450040

Identification

Category	Connector
Series	HARTING PushPull
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Compact With board locks With integrated seal

Version

Locking type	PushPull
Details	for vertical RJ jack 09 45 551 1103

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4
----------------	---------------------------

Commercial data

Packaging size	100
Net weight	2.98 g
Country of origin	Romania
European customs tariff number	85366990