


## D-SUB EMC inner sleeve - VS-09-TI-2EMV - 1688476

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



D-SUB EMC inner sleeve, for sleeve housing VS-09-..., shell size 1, shielded

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 876388
GTIN	4017918876388
Weight per Piece (excluding packing)	20.890 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Mechanical characteristics

Number of positions	9
Cable outlet	Angled
Color	Bare metallic
Type	D-SUB 9
Size of housing	1

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

#### Material data

Housing material	Nickel silver
Height	16.9 mm

#### Electrical characteristics

# D-SUB EMC inner sleeve - VS-09-TI-2EMV - 1688476

## Technical data

### Electrical characteristics

Number of positions	9
---------------------	---

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440213
eCl@ss 9.0	27440213

### ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC001132
ETIM 4.0	EC002641
ETIM 5.0	EC001133
ETIM 6.0	EC001133

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

## D-SUB EMC inner sleeve - VS-09-TI-2EMV - 1688476

### Approvals

---

#### Approval details

EAC		B.01742
-----	---	---------

---