

## 4 Port USB to DB9 RS232 Serial Adapter Hub – Industrial DIN Rail and Wall Mountable

Product ID: ICUSB2324I



The ICUSB2324I 4-Port Industrial USB to Serial Hub with DIN Rail Clips converts a single USB port into four RS232 serial ports, enabling you to connect to, monitor and control your serial devices.

Featuring rugged metal construction, with sturdy wall-mounting brackets and top-hat DIN Rail clips (included), this USB to Serial Hub provides versatile mounting options and a robust solution for both harsh industrial environments and simple desktop installations.

This USB powered adapter also retains assigned serial COM port values once connected, allowing the same values to be automatically reassigned to the ports provided by the adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

### Features

- 4-port USB to RS232 serial adapter
- Rugged metal construction
- Wall-mountable, with included DIN Rail clips
- COM retention: COM Port assignments maintained across reboot
- Baud Rate up to 921.6 Kbps
- Powered by an available USB port - no external power adapter required

<b>Hardware</b>	Warranty	2 Years
	Bus Type	USB 2.0
	Chipset ID	FTDI - FT4232HL
	Interface	Serial
	Port Style	External Hub
	Ports	4
<b>Performance</b>	Data Bits	7, 8
	FIFO	256 Bytes
	Max Baud Rate	921.6 Kbps
	Maximum Data Transfer Rate	921.6Kbps
	MTBF	282713.5 hours
	Parity	Odd, Even, Mark, Space, None
	Serial Protocol	RS-232
	Stop Bits	1, 2
<b>Connector(s)</b>	Connector Type(s)	1 - USB B (4 pin) Female 4 - DB-9 (9 pin, D-Sub) Male
<b>Software</b>	OS Compatibility	Windows® CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
<b>Indicators</b>	LED Indicators	4 - Each, Tx/Rx Activity indicators
<b>Power</b>	Plug Type	M
	Power Source	USB-Powered
<b>Environmental</b>	Humidity	5~95% RH
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-20°C to 85°C (-4°F to 185°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	0.9 in [23.2 mm]
	Product Length	7 in [178 mm]
	Product Weight	10.6 oz [300 g]

	Product Width	2.3 in [59 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	18.3 oz [518 g]
<b>What's in the Box</b>	Included in Package	1 - USB to RS-232 Serial Adapter 1 - DIN rail kit 1 - 6 ft USB A to B cable 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.