

tesa® 60672

Robust aluminum tape with paper liner - 75µ foil

tesa® 60672 is a robust aluminum tape based on a 75 µm (3 mil) aluminum foil, a transparent acrylic adhesive and a white, single-sided siliconized, 85µm thick paper liner

Features:

- Mechanical stable
- Easily removable liner
- Suitable for permanent applications
- Barrier against moisture, gases and vapors
- Electrically and thermally conductive
- Aging resistant
- Heat and light reflective
- Flame retardant according to DIN 4102, class B1
- Flame retardant according to the requirements in UL 510A
- Meets requirements of UL723

Main Application

- Repairs on trucks and trailers
- Joining and sealing of thermal insulation, ducts and pipes
- To make substrates electrically and thermally conductive
- To reflect heat radiation

Technical Data

▪ Backing material	aluminium foil	▪ Tensile strength	60 N/cm
▪ Total thickness	125 µm	▪ Thickness of liner	85 µm
▪ Type of adhesive	acrylic	▪ Temperature resistance min.	-40 °C
▪ Adhesion to steel	10 N/cm	▪ Temperature resistance max.	160 °C
▪ Elongation at break	8 %		

Adhesion to

▪ Glass (initial)	10.0 N/cm	▪ PVC (initial)	7.0 N/cm
▪ PE (initial)	5.5 N/cm		

Properties

▪ Hand tearability	●●●●	▪ Abrasion resistance	●●●●
▪ Suitable for die cutting	yes	▪ Water resistance	●●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=60672>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

tesa® 60672

Robust aluminum tape with paper liner - 75µ foil

Additional Information

The total thickness given in the section "Technical Data" describes the thickness of the tape without liner. The thickness with liner is 210 µm (8.3 mil).

For latest information on this product please visit <http://l.tesa.com/?ip=60672>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

