

TYROLA



ESD safety boots

SIZE 35-48

- 4.5 mm studs for maximum grip on all flooring
- Two-fabric upper with orange inserts to highlight the design
- Reflective insert at the heel for better visibility
- ESD Parade shoe: 2 to 15 MΩ



■ 2844 Black

COMPOSITION

Upper	Full-grain leather + Microfiber
Lining	Textile
Toe Cap	Polycarbonate
Stay clean insole	Mesh and ESD PU foam. Removable. Anatomic. Antibacterial. Antifungal.
Puncture proof insert	Non-metallic
Sole	Double density PU/PU
Weight for size 37*	470g
Weight for size 42*	590g

* Weight per shoe

THE + PARADE EXCLUSIVE TECHNOLOGIES



The sole design supports the natural arch of the foot for greater comfort and less tiredness in an upright position.



An exclusive technology that absorbs the impact for you and provides greater comfort day in day out.



An encapsulated air bubble absorbs the micro-impacts of walking.

S3 WET AND RISK FLOOR • NORM: EN ISO 20345: 2011

- Toe cap (200J)
- Antipuncture sole
- Antislip sole **
- Shock-absorption
- Antistatic
- Oil and fuel resistant shoe
- Water-repellent upper

THE + ADDITIONAL FEATURES



Non-magnetic



Electrostatic dissipation

**	COEFFICIENT OBTAINED FOR SIZE 42	FLAT		HEEL	
		NORM	PARADE	NORM	PARADE
	SRA Antislip Ceramic / Nals (soap solution)	0,32	0,37	0,28	0,34
	SRB Antislip steel / Glycerine (oil)	0,18	0,27	0,13	0,14