

ECI-63.60-D00-K4 -



#### Characteristics of the drive solution

Typ	Unit	Value
Order number	-	VM.ECI6360DK4
Weight	kg	1.5
Length	mm	158
Ambient temperature	-	0°C to +40°C
Protection	-	IP 54

#### Motor

Typ	Unit	Value
Type of motor	-	brushless EC motor, internal rotor
Motor designation	-	ECI-63.60-D00-K4
Voltage	V	48
Output speed	rpm	4000
Nominal power	W	356.0
Rated current	A	8.3
Torque	Ncm	85.0
Operating capacitor	-	no
weight of Motor	kg	1.5