

## Cutting tool - CUTFOX-CD - 1212474

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable duct cutter, for cutting plastic cable ducts, covers, and profiles, 45° limit stop also for bevel cuts, 75 mm cutting length

### Your advantages

- ✓ Easy, burr-free cutting with minimum effort thanks to the special cutting geometry and optimum leverage
- ✓ Non-slip ergonomic handle
- ✓ 45° limit stop
- ✓ 75 mm cutting width
- ✓ With spring reset

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 527026
GTIN	4046356527026
Weight per Piece (excluding packing)	0.439 kg
Custom tariff number	82015000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	245 mm
Blade width	75 mm
Cable diameter	> 0 mm

#### General

Color	black
Weight	0.43 kg
Min. cross section	0 mm <sup>2</sup>

### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

# Cutting tool - CUTFOX-CD - 1212474

## Classifications

### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	24330900
eCl@ss 6.0	21040600
eCl@ss 7.0	21044727
eCl@ss 8.0	21044727
eCl@ss 9.0	21043716

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000160
ETIM 5.0	EC000160
ETIM 6.0	EC000160
ETIM 7.0	EC000160

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

