



Datasheet

RS Pro 80° paper masking tape 12mmx50m

Stock number: 1846803

EN



General Description

A lightly creped paper tape coated with a solvent based rubber - resin adhesive.

Features

- Easy unwind and tear
- Low tack
- Clean peel from most surfaces up to 12 Hours
- Good high temperature resistance

Technical Details	Typical Values
Thickness	0.12 mm
Breaking Load	30 N/cm
Elongation	9%
Adhesion to steel	2.6 N/cm
RoHS compliant	Yes
Service Temperature	0°C to +80°C
Application Temperature	+5°C to +40°C
Storage Temperature	+12°C to +25°C

STORAGE

Tapes stored below the minimum recommended temperature will require warming up to that level before use. Up to 24 hours may be required for this to take place.