



Datasheet

RS Pro Zirconium Flap Disc - 115mm x 22.23mm x 80g - 13,300rpm

RS Stock No: **184-9843**



Product Details

Premium quality Zirconium grain flap discs are engineered for maximum performance stock removal, blending and finishing. The lightweight fibreglass backing absorbs vibration and makes this product incredibly strong and durable. Pro-line Zirconium flap discs are long life & suitable for a full range of metal applications including stainless steel. RS Pro Zirconium Flap Discs discs are manufactured to O.S.A. Safety standards

Features and Benefits

- 13,300 Maximum RPM
- Manufactured to O.S.A Safety Standards
- Suitable for use on Stainless Steel, Mild Steel, Sheet Metal and High Grade Steel

Specifications:

Abrasive Material	Zirconium
Backing Type	T29 (Fibreglass)
Bore Size	22.23mm
Disc Diameter	115mm
Grit Size	80
Maximum Safe Speed	13,300rpm
Number of Pieces	1
Suitable for	Steel & Stainless Steel

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.