

FH202 S A-40/0,03



FH202 S A-40/0,03 Residual Current Circuit Breaker



General Information

Extended Product Type	FH202 S A-40/0,03
Product ID	2CSF202124R1400
EAN	8012542647638
Catalog Description	FH202 S A-40/0,03 Residual Current Circuit Breaker
Long Description	The RCCBs FH200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous AC and A types is particularly suitable for installation in domestic applications. Screwless version.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Popular Downloads

Data Sheet, Technical Information	2CSC400030D0202
Instructions and Manuals	Printed on product

Dimensions

Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.200 kg

Technical

Standards	IEC/EN 61008
Operating Characteristic	Instantaneous
Type of Residual Current	A type
Rated Residual Current	30 mA
Rated Current (I_n)	40 A
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 2.4 W

