

297352



# Aluminium telescopic waterfed handle, 1600 - 2780 mm, Ø31 mm, Black



This professional telescopic water-fed handle (1600–2840 mm) has an insulated sleeve for a comfortable grip and a tapered hose connector. Maximum water pressure, 6 bars.

# Technical Data

Item Number	297352
Material	Anodised Aluminium Polypropylene Chromium-plated brass
Meets the REACH Regulation (EC) No. 1907/2006	Yes **
Use of Phthalates	No
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	500 Pcs.
Quantity Per Layer (Pallet)	25 Pcs.
Box Length	1650 mm
Box Width	140 mm
Box Height	85 mm
Product Diameter	31 mm
Length/Depth	1600 mm
Width	31 mm
Height	31 mm
Max. Length	2780 mm
Gross Weight	1,09 kg
Net Weight	1,02 kg
Cubik metre	0,0016 M3
Max. bars pressure	6 Bar
Max usage temperature (non food contact)	50 °C
Min. pH-value in usage concentration	4 pH
Max. pH-value in Usage Concentration	11 pH
GTIN-13 Number	5705022973015
GTIN-14 Number (Box quantity)	15705022973012
Commodity Code	76082020
Country of origin	Denmark

\*\* Lead (Pb, CAS: 7439-92-1) is on the REACH candidate list as a Substance of Very High Concern (SVHC). This product contains lead (Pb) in a concentration above 0.1% w/w. Consequently the REACH Regulation (EC) No. 1907/2006 require Vikan to notify our customers of the content of lead.