



COBArib

Anti-slip fluted rubber matting

- Durable, manufactured from hardwearing natural rubber.
- Fine ribbed surface has effective slip-resistance.
- Provides insulation from cold concrete floors.
- Has some noise insulation properties.
- Can also be used on workbenches.
- Available in a chunky **COBArib Wide** option.

Product height: 3mm or 6mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 10 (3mm)	30	20 x 20 x 90	Roll	1	20	Black	RR010010
0.9 x per linear metre (3mm)	3	2 x 2 x 90	Roll	1	N/A	Black	RR010010C
1.2 x 10 (3mm)	40	20 x 20 x 120	Roll	1	20	Black	RR010020
1.2 x per linear metre (3mm)	4	2 x 2 x 120	Roll	1	N/A	Black	RR010020C
0.9 x 10 (6mm)	73	28 x 28 x 90	Roll	1	9	Black	RR010030
0.9 x per linear metre (6mm)	6	28 x 28 x 90	Roll	1	N/A	Black	RR010030C
1.2 x 10 (6mm)	8	28 x 28 x 120	Roll	1	9	Black	RR010040
1.2 x per linear metre (6mm)	8	28 x 28 x 120	Roll	1	N/A	Black	RR010040C

Material: Natural rubber
 Surface Finish: Fine fluted ribbed surface
 Product Height: 3 mm and 6 mm nominal

Operating Temperature: -20° to 80° C

Resistance to Chemicals: Resistant to water and most mild acids
 Environmental Resistance: Use in wet or dry areas.
 UV Resistance: Yes

Typical Applications: Industrial uses around benches, workstations and walkways. Also suitable for use as a covering for bench work surfaces.

Installation Method: Loose lay
 Cleaning method: Hose down or pressure wash using a mild detergent.

Continued on next page

United Kingdom

COBA Europe Ltd
 Marlborough Drive
 Fleckney, Leicestershire
 LE8 8UR

+44 (0)116 240 1088
 sales@cobaeurope.com
 www.cobaeurope.com

Germany

COBA Europe GmbH
 Pullenweg 1 - 3
 41352 Korschenbroich

+49 (2161) 2945-0
 verkauf@cobaeurope.de
 www.cobaeurope.de

Slovakia

COBA Europe s.r.o.
 Terchová - Vyšné Kamence 11
 SK-013 06

+421 41 507 11 12
 sales@cobaeurope.sk
 www.cobaeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.


Product Performance:

Fatigue:

Slip Resistance:

Wear:

Low ≠ High



Flame Retardancy:

N/A

Country of Origin:

China

Chemical Data

Major components: Styrene-Butadiene Rubber (SBR) Carbon black

Minor components: Zinc Oxide ,Sulfur, Accelerators / Activators (< 1 %),Antioxidant / Stabilizers (< 1 %)

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeeurope.com
www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeeurope.de
www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

+421 41 507 11 12
sales@cobaeeurope.sk
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.