



- ① HOUSING FULLY LOADED WITH CONTACTS.
- ② NUMBER ON CONTACT INDICATES WIRE RANGE.
- ③ CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- ④ .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑤ .000001 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑥ .000020 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑦ .000050 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 BRIGHT TIN OR BRIGHT TIN-LEAD IN AREA SHOWN. .000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑧ SPECIAL DATE CODE IN THIS APPROXIMATE AREA. A; MM = MONTH; Y = LAST DIGIT OF YEAR.
- ⑨ .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 MATTE TIN IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑩ .000001 MIN GOLD ON MATING END FOR .100 MIN LENGTH. .000100-.000200 MATTE TIN IN AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑪ OBSOLETE

STANDARD	.125 .115	⑩	2	#22-26	2-745495-0
STANDARD	.125 .115	⑨	3	#20-22	1-745495-9
STANDARD	.125 .115	⑨	2	#22-26	1-745495-8
STANDARD	.125 .115	⑨	1	#26-30	1-745495-7
SMALL PACK	.125 .115	⑤	2	#22-26	1-745495-6
STANDARD	.125 .115	⑦	2	#22-26	1-745495-4
STANDARD	.125 .115	⑥	2	#22-26	1-745495-3
STANDARD	.156 .146	⑤	3	#20-22	1-745495-2
			2	#22-26	1-745495-1
			1	#26-30	1-745495-0
STANDARD	.156 .146	④	3	#20-22	745495-9
			2	#22-26	745495-8
			1	#26-30	745495-7
STANDARD	.125 .115	⑤	3	#20-22	745495-6
			2	#22-26	745495-5
			1	#26-30	745495-4
STANDARD	.125 .115	④	3	#20-22	745495-3
			2	#22-26	745495-2
			1	#26-30	745495-1
PACKAGING	H	CONTACT FINISH	②	AWG WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. TOLERANCES UNLESS OTHERWISE SPECIFIED:

DIMENSIONS: INCHES	0 PLC ± -	1 PLC ± -	2 PLC ± -	3 PLC ± .005	4 PLC ± -	ANGLES ± -
--------------------	-----------	-----------	-----------	--------------	-----------	------------

MATERIAL: SEE CALL OUT. FINISH: -

WEIGHT: -

CUSTOMER DRAWING

DIN J GALLUCCI BG 3-19-90  
CHK H. MOLL 4-12-90

APVD: -

NAME: -

PRODUCT SPEC: -

APPLICATION SPEC: -

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 745495

RESTRICTED TO: -

SCALE: 4:1

SHEET: 1 OF 1

REV: S1

STE TE Connectivity

RECEPTACLE ASSEMBLY, METAL SHELL, SIZE 3, 25 POSITION.