## **Hydraulic Oil, Manifolds and Fittings**



## 3/8" Swivel Connector

360 degree swivel coupler for optimal orientation of the hydraulic connection on cylinders, pumps and hoses. Order Model Nr. XSC-1.

A, AM BFZ FZ HF Series



					Series	•	a fill and a second
700 bar Fittings		Model Number		ensions (mm)	Octios		
Street Elbow		ī	A	В	С	D	В
From: %"-NPTF Male	1 画文	FZ-1616	23	33	3/8"-18 NPTF	3/8"-18 NPTF	
To: %"-NPTF Female		12-1010	20		70 10141 11	78 10141 11	A
							<u></u>
Reducing Connector							_ A _
From: %"-NPTF Female	7 5	FZ-1615	28	25	%"-18 NPTF	1/4"-18 NPTF	
To: 1/4"-NPTF Female		F7 400F	47	29	1/ II 4 4 NIDTE	2/II 40 NDTE	CIDI
From: ½"-NPTF Female To: %"-NPTF Female	All Carlos	FZ-1625	47	29	½"-14 NPTF	3%"-18 NPTF	B <b>ℱ</b>
Hexagon Nipple	7777						. A
From: To:	50	FZ-1608	38	16	1/4"-18 NPTF	1/4"-18 NPTF	
3%"-NPTF 3%"-NPTF	The state of the s	FZ-1608	51	19	3/8"-18 NPTF	3/8"-18 NPTF	
%"-NPTF	-	FZ-1617	37	19	3/8"-18 NPTF	3/8"-18 NPTF	<u> </u>
Coupling					78 - 10 INF II	78 - 10 INF 11	Δ.
From: To:	4000						· A
%"-NPTF %"-NPTF		FZ-1614	29	23	3/8"-18 NPTF	%"-18 NPTF	c D
1/4"-NPTF 1/4"-NPTF	All Sales	FZ-1605	29	19	1/4"-18 NPTF	1/4"-18 NPTF	B/
		12 1000		1.0	74 1011111	74 1011111	
Cross		FZ-1613	45	25	3/8"-18 NPTF		
From: %"-NPTF Female To: %"-NPTF Female	The state of the s	12-1010	45	25	98 - 10 INF IF	_	BI CI
75 111 11 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	- Transfer				_		L A J
Tee							-C
From: To:		<b>F7</b> 4040	45	0.5	2/11 40 NDTE		
%"-NPTF %"-NPTF 1/4"-NPTF 1/4"-NPTF	200	FZ-1612 FZ-1637	45 45	25 24	3%"-18 NPTF	-	
	1	FZ-1037	45	24	1/4"-18 NPTF	_	L A
Street Tee							. A .
From: %"-NPTF Female	6 E.	BFZ-16312	56	26	%"-18 NPTF	%"-18 NPTF	D C
To: %"-NPTF Male							С
Elbow	The second second						
From: To:							A
%"-NPTF %"-NPTF	The state of the s	FZ-1610	33	20	3/8"-18 NPTF	_	C
1/4"-NPTF 1/4"-NPTF	-	FZ-1638	36	24	1/4"-18 NPTF	_	C. B
	-	12 1000	-		74 1014111		
Reducer	200						_ A _
From: To: %"-NPTF	PATE	FZ-1630	19	19	1/4"-18 NPTF	%"-18 NPTF	
1/4"-NPTF 1/2"-NPTF	AMINE	BFZ-1630	28	22	1/4"-18 NPTF	½"-14 NPTF	C
3/8"-NPTF G1/4"		BFZ-16301	19	19	G1/4"	3/8"-18 NPTF	<u>Β</u> /−
Adaptor		2.2.000.			G/4	78 - 10 INI 11	
From: To:							^
G1/4" 1/4"-NPTF	-	BFZ-16411	35	19	1/4"-18 NPTF	G1/4"	
G¼" 1/8"-NPTF	- Tomas	BFZ-16421	31	19	1/8"-27 NPTF	G1/4"	CDDD
G3/8" 1/4"-NPTF		BFZ-16323	43	24	1/4"-18 NPTF	G3%"	, <u>B</u>
G3/8" 3/8"-NPTF	1	BFZ-16324	43	24	3/8"-18 NPTF	G%"	
Adaptor					/5 /5/11/11		
From: To:							A .
1/4"-NPTF	No.	FZ-1055	44	23	1/4"-18 NPTF	3/8"-18 NPTF	character
1/4"-NPTF 1/8"-NPTF		FZ-1642	30	19	1/8"-27 NPTF	1/4"-18 NPTF	
½"-NPTF %"-NPTF	100000	FZ-1634	42	28	3/8"-18 NPTF	½"-18 NPTF	₽/
Swivel Fitting		30 .			,		
From: 3/8"-NPTF Male	200-	FZ-1660	40	22	%"-18 NPTF	%"-18 NPTF	A .
To: %"-NPTF Female							C D
							<u>B</u> _/
				i .			

www.enerpac.com ENERPAC @ 125