



ABAC Mii-DTL-38999 Series III Connector

RS COMPONENTS Connector & Screen Trap Part Number Matrix



Description	RS Part Number	ABAC Part Number	D38999 QPL Part Number	Shell Size	Screen Trap Backshell							
					Straight				Right Angle			
					RS Part	Small	RS Part	Large	RS Part	Small	RS Part	Large
D38999, Wall mounting, Size 9, A35, Pin	7450941	ABAC20W0935PN	D38999/20WA35PN	09	7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Wall mounting, Size 9, A35, Socket	7450944	ABAC20W0935SN	D38999/20WA35SN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Wall mounting, Size 9, A98, Pin	7450948	ABAC20W0988PN	D38999/20WA98PN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Wall mounting, Size 9, A98, Socket	7450957	ABAC20W0988SN	D38999/20WA98SN	11	7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Wall mounting, Size 11, B35, Pin	7450950	ABAC20W1135PN	D38999/20WB35PN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Wall mounting, Size 11, B35, Socket	7450954	ABAC20W1135SN	D38999/20WB35SN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Wall mounting, Size 11, B98, Pin	7450963	ABAC20W1198PN	D38999/20WB98PN	13	7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Wall mounting, Size 11, B98, Socket	7450966	ABAC20W1198SN	D38999/20WB98SN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Wall mounting, Size 13, C35, Pin	7450960	ABAC20W1335PN	D38999/20WC35PN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Wall mounting, Size 13, C35, Socket	7450979	ABAC20W1335SN	D38999/20WC35SN	15	7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Wall mounting, Size 13, C98, Pin	7450972	ABAC20W1398PN	D38999/20WC98PN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Wall mounting, Size 13, C98, Socket	7450976	ABAC20W1398SN	D38999/20WC98SN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Wall mounting, Size 15, D35, Pin	7450985	ABAC20W1535PN	D38999/20WD35PN	17	7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Wall mounting, Size 15, D35, Socket	7450988	ABAC20W1535SN	D38999/20WD35SN		7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Wall mounting, Size 17, E35, Pin	7450982	ABAC20W1735PN	D38999/20WE35PN		7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17
D38999, Wall mounting, Size 17, E35, Socket	7450991	ABAC20W1735SN	D38999/20WE35SN	09	7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17
D38999, Panel Mounting, Size 9, A35, Pin	7450994	ABAC24W0935PN	D38999/24WA35PN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Panel Mounting, Size 9, A35, Socket	7450998	ABAC24W0935SN	D38999/24WA35SN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Panel Mounting, Size 9, A98, Pin	7451001	ABAC24W0988PN	D38999/24WA98PN	11	7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Panel Mounting, Size 9, A98, Socket	7451004	ABAC24W0988SN	D38999/24WA98SN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Panel Mounting, Size 11, B35, Pin	7451008	ABAC24W1135PN	D38999/24WB35PN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Panel Mounting, Size 11, B35, Socket	7451017	ABAC24W1135SN	D38999/24WB35SN	13	7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Panel Mounting, Size 11, B98, Pin	7451010	ABAC24W1198PN	D38999/24WB98PN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Panel Mounting, Size 11, B98, Socket	7451014	ABAC24W1198SN	D38999/24WB98SN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Panel Mounting, Size 13, C35, Pin	7451023	ABAC24W1335PN	D38999/24WC35PN	15	7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Panel Mounting, Size 13, C35, Socket	7451026	ABAC24W1335SN	D38999/24WC35SN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Panel Mounting, Size 13, C98, Pin	7451020	ABAC24W1398PN	D38999/24WC98PN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Panel Mounting, Size 13, C98, Socket	7451039	ABAC24W1398SN	D38999/24WC98SN	17	7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Panel Mounting, Size 15, D35, Pin	7451032	ABAC24W1535PN	D38999/24WD35PN		7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Panel Mounting, Size 15, D35, Socket	7451036	ABAC24W1535SN	D38999/24WD35SN		7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Panel Mounting, Size 17, E35, Pin	7451045	ABAC24W1735PN	D38999/24WE35PN	09	7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17
D38999, Panel Mounting, Size 17, E35, Socket	7451048	ABAC24W1735SN	D38999/24WE35SN		7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17
D38999, Plug, Size 9, A35, Pin	7451042	ABAC26W0935PN	D38999/26WA35PN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Plug, Size 9, A35, Socket	7451051	ABAC26W0935SN	D38999/26WA35SN	11	7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Plug, Size 9, A98, Pin	7451054	ABAC26W0988PN	D38999/26WA98PN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Plug, Size 9, A98, Socket	7451058	ABAC26W0988SN	D38999/26WA98SN		7600503	ABAC1003W09	7600512	ABAC1005W09	7600569	ABAC0703W09	7600578	ABAC0705W09
D38999, Plug, Size 11, B35, Pin	7451067	ABAC26W1135PN	D38999/26WB35PN	13	7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Plug, Size 11, B35, Socket	7451060	ABAC26W1135SN	D38999/26WB35SN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Plug, Size 11, B98, Pin	7451064	ABAC26W1198PN	D38999/26WB98PN		7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Plug, Size 11, B98, Socket	7451073	ABAC26W1198SN	D38999/26WB98SN	15	7600515	ABAC1005W11	7600519	ABAC1007W11	7600571	ABAC0705W11	7600575	ABAC0707W11
D38999, Plug, Size 13, C35, Pin	7451076	ABAC26W1335PN	D38999/26WC35PN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Plug, Size 13, C35, Socket	7451070	ABAC26W1335SN	D38999/26WC35SN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Plug, Size 13, C98, Pin	7451089	ABAC26W1398PN	D38999/26WC98PN	17	7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Plug, Size 13, C98, Socket	7451082	ABAC26W1398SN	D38999/26WC98SN		7600528	ABAC1007W13	7600521	ABAC1009W13	7600584	ABAC0707W13	7600587	ABAC0709W13
D38999, Plug, Size 15, D35, Pin	7451086	ABAC26W1535PN	D38999/26WD35PN		7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Plug, Size 15, D35, Socket	7451095	ABAC26W1535SN	D38999/26WD35SN	09	7600525	ABAC1009W15	7600534	ABAC1011W15	7600581	ABAC0709W15	7600590	ABAC0711W15
D38999, Plug, Size 17, E35, Pin	7451098	ABAC26W1735PN	D38999/26WE35PN		7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17
D38999, Plug, Size 17, E35, Socket	7451092	ABAC26W1735SN	D38999/26WE35SN		7600537	ABAC1011W17	7600531	ABAC1013W17	7600593	ABAC0711W17	7600597	ABAC0713W17

Cable Entry	
Example	ABAC1003W09 = 4.7mm
Cable entry Ref.	Cable entry up to (mm)
03	4.7
04	6.3
05	7.9
06	9.5
07	11.1
08	12.7
09	14.2
10	15.8
11	17.4
12	19
13	20.6
14	22.2
15	23.8
16	25.4
17	27
18	28.6
19	30.2
20	31.8
21	33.3

Asia Europe | Americas
www.ttabcconnectors.com | www.abinterconnect.com

© Copyright TT electronics, 2012. All rights reserved. Subject to change without prior notification. Issue: 2012.1

