

64210CBI

COOL BLUE INTENSE | Halogen headlight lamps for cars



Areas of application

- Headlight
- Ideal for use in clear-glass headlights

Product benefits

- Stylish look
- Up to 20 % more light (compared to standard halogen lamps)
- Bluish white light for xenon look

Product features

- Color temperature: up to 4,200 K
- High luminous flux
- Headlight lamp for bluest legally approved halogen light
- Modern design with a silver cap (H4/H7)

Technical data

Electrical data


Power input	58 W ¹⁾
Nominal wattage	55.00 W
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Photometrical data

Color temperature	4100 K
Luminous flux	1500 lm
Luminous flux tolerance	±10 %

Dimensions & weight



Product line drawing

Length	59.0 mm
Diameter	12.0 mm
Product weight	12.50 g

Lifespan

Lifespan B3	100 h
Lifespan Tc	200 h

Additional product data

Base (standard designation)	PX26d
-----------------------------	-------

Product datasheet

Certificates & standards

ECE category	H7
--------------	----

Country specific categorizations

Order reference	64210CBI 55W 12
-----------------	-----------------

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321650757	64210CBI	Hard Cover Box 2	95 mm x 47 mm x 115 mm	0.51 dm ³	109.00 g
4008321650764	64210CBI	Shipping carton box 20	240 mm x 106 mm x 250 mm	6.36 dm ³	1250.00 g
4008321651341	64210CBI	Folding carton box 1	34 mm x 34 mm x 58 mm	0.07 dm ³	8.00 g
4008321651358	64210CBI	Bundle 10	174 mm x 58 mm x 68 mm	0.69 dm ³	155.00 g
4008321651365	64210CBI	Shipping carton box 100	186 mm x 129 mm x 356 mm	8.54 dm ³	1727.00 g
4008321651372	64210CBI	Blister 2	83 mm x 35 mm x 117 mm	0.34 dm ³	42.00 g
4008321651389	64210CBI	Shipping carton box 20	218 mm x 145 mm x 294 mm	9.29 dm ³	554.67 g
4008321651396	64210CBI	Unpacked 1	30 mm x 17 mm x 32 mm	0.02 dm ³	19.00 g
4008321651402	64210CBI	Shipping carton box 180	255 mm x 240 mm x 345 mm	21.11 dm ³	2689.00 g
4008321651563	64210CBI	Blister 1	65 mm x 47 mm x 135 mm	0.41 dm ³	21.00 g
4008321651570	64210CBI	Shipping carton box 10	116 mm x 143 mm x 279 mm	4.63 dm ³	318.00 g
4008321660367	64210CBI	Hard Cover Box 2	- x - x -		
4008321660374	64210CBI	Shipping carton box 20	106 mm x 240 mm x 250 mm	6.36 dm ³	1230.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.