



Safetyplugs

Toughplugs

NON STANDARD



646 WHI



647 CHA



655 BLK



646 CHA



647 WHI



655 ORG



647 CHA



655 D8 RED

Established range of plugs and adaptors.

The established names of Safetyplug,[™] Toughplug[™] and Duraplug[®] strengthen MK's reputation for high quality products with the accent on safety and quality.

646 WHI	10
646 CHA FITTED WITH 13 AMP FUSE	10
646/3 WHI FITTED WITH 3 AMP FUSE	10
645 NIP SECRET SCREW FOR SAFETYPLUG AND TOUGHPLUG	100
644 ZIC KEY FOR SECRET SCREW	10

See page 59 for spare fuse links.
BS.1363 Pt.1: 1995

647 WHI	10
647 CHA FITTED WITH 13 AMP FUSE	10

See page 59 for spare fuse links.
For use only with MK non-standard
13 amp socket outlets.

655 WHI FITTED WITH 13 AMP FUSE	10
655/3 WHI FITTED WITH 3 AMP FUSE	10
655 BLK	10
655 ORG	10
655 RED FITTED WITH 13 AMP FUSE	10
655 D8 WHI	10
655 D8 RED MARKED 'HOSPITAL PROPERTY'. FITTED WITH 13 AMP FUSE	10

See page 59 for spare fuse links.
BS.1363/A Pt.1: 1995

Rubber Plugs

Round Pin Plugs

Plug Adaptors

13 AMP

ROUND PIN



PF133 WHI



PF133 ORG



PF133 BLK



P53 BLK



P153 BLK



505 WHI



515 WHI



641 WHI



690 WHI



692 WHI



696 WHI



698 PPK

PF 133 WHI
PF 133 ORG
PF 133 BLK
FITTED WITH
13 AMP FUSE

10
10
10

P 53 BLK
5 AMP
P 153 BLK
15 AMP

10
10

502 WHI
2 AMP
505 WHI
5 AMP
515 WHI
15 AMP
RESILIENT COVER
639 WHI
2 AMP FUSED
641 WHI
5 AMP FUSED
643 WHI
15 AMP
FITTED WITH 5 AMP FUSE

10
10
10
10
10
10

690 WHI
13 AMP
WITH 1 X 13A
AND 1 COMBINED 16A UNIVERSAL
AND GERMAN TYPE 2P+E
SOCKET OUTLET
FUSED 13 AMP

5

692 WHI
13 AMP
WITH 3 X 13A SOCKET OUTLETS
FUSED 13 AMP
696 WHI
13 AMP
WITH 2 X 13A SOCKET OUTLETS
UNFUSED
698 PPK
13 AMP
WITH 1 X 1A
SHAVER SOCKET OUTLET
FUSED 1 AMP

5
5
10

With rubber cover and
ABS/Polycarbonate base.
Colour coded sleeves
on the pins.

Available with alternative fuse
ratings to special order only.
BS.1363/A Pt.1: 1995

P 53 BLK
Manufactured in rubber.

P 153 BLK
With rubber cover and
ABS/Polycarbonate base.
BS.546: 1950

See page 59 for spare
fuse links to BS.646.
BS.546: 1950

BS.1363 Pt.3: 1995

BS.1363 Pt.3: 1995