



OUR OFFER

GEFRAN - PID CONTROLLER 650/1250

GEFRAN 650 - 1250

PID Controller with a large LCD Display and IP65 protection

650 Series - 48x48 mm - 100-240 Vac/dc

Stock No.	Gefran MPN	Out	Output Type
862-6619	F060558	2	1 Relay, 1 Logic
862-6613	F059574	2	2 Relay
862-6584	F060562	3	2 Relay, 1 Logic
862-6631	F065788	3	3 Relay
862-6596	F065790	3	2 Relay, 1 Logic
862-6629	F060567	3	2 Relay, 1 Logic
862-6622	F060564	3	2 Relay, 1 Analogue
862-6590	F065791	3	2 Relay, 1 Analogue
862-6593	F060563	4	3 Relay, 1Logic
862-6635	F065792	4	4 Relay



650 Series - 48x48 mm - 20-27 Vac/dc

Stock No.	Gefran MPN	Out	Output Type
862-6543	F065795	2	1 Relay, 1 Logic
862-6546	F065796	2	2 Relay
862-6540	F065798	3	2 Relay, 1 Logic
862-6559	F065799	3	3 Relay
862-6552	F065801	3	2 Relay, 1 Logic
862-6638	F065802	3	2 Relay, 1 Logic
862-6625	F065803	3	2 Relay, 1 Analogue
862-6556	F065804	3	1 Relay, 1 Logic, 1Analogue
862-6565	F065808	4	4 Relay
862-6568	F065809	4	3 Relay, 1Logic
862-6562	F065810	4	3 Relay, 1 Logic

1250 Series - 48x96 mm - 100-240 Vac/dc

Stock No.	Gefran MPN	Out	Output Type
862-6571	F060836	2	1 Relay, 1 Logic
862-6574	F060837	2	2 Relay
862-6578	F060839	3	2 Relay, 1 Logic
862-6587	F060840	3	3 Relay
862-6603	F060841	3	2 Relay, 1 Logic
862-6580	F060843	3	3 Relay, 1 Logic
862-6607	F060845	3	2 Relay, 1 Analogue
862-6600	F060847	3	3 Relay, 1 Logic



1250 Series - 48x96 mm - 20-27 Vac/dc

Stock No.	Gefran MPN	Out	Output Type
862-6650	F060861	2	1 Relay, 1 Logic
862-6644	F060862	2	2 Relay
862-6647	F060865	3	3 Relay
862-6641	F060870	3	2 Relay, 1 Analogue

For more technical information please visit:

www.rs-online.com