



## OUR OFFER

# SIEMENS – SIMATIC S7-1200

## SIMATIC S7-1200

A modular, compact and versatile controller

### PLC CPU

Stock-No.	Siemens-MPN	Type	In/Out	Output	Voltage
862-4455	6ES7211-1BE40-0XB0	CPU 1211C, AC/DC/Relay	6/4	Relay	85 - 264 Vac
862-4459	6ES7211-1AE40-0XB0	CPU 1211C, DC/DC/DC	6/4	Transistor	24 Vdc
862-4468	6ES7211-1HE40-0XB0	CPU 1211C, DC/DC/Relay	6/4	Relay	24 Vdc
862-4461	6ES7212-1BE40-0XB0	CPU 1212C, AC/DC/Relay	8/6	Relay	85 - 264 Vac
862-4465	6ES7212-1AE40-0XB0	CPU 1212C, DC/DC/DC	8/6	Transistor	24 Vdc
862-4474	6ES7212-1HE40-0XB0	CPU 1212C, DC/DC/Relay	8/6	Relay	24 Vdc
862-4477	6ES7214-1BG40-0XB0	CPU 1214C, AC/DC/Relay	14/10	Relay	85 - 264 Vac
862-4471	6ES7214-1AG40-0XB0	CPU 1214C, DC/DC/DC	14/10	Transistor	24 Vdc
862-4480	6ES7214-1HG40-0XB0	CPU 1214C, DC/DC/Relay	14/10	Relay	24 Vdc
862-4483	6ES7215-1BG40-0XB0	CPU 1215C, AC/DC/Relay	14/10	Relay	85 - 264 Vac
862-4487	6ES7215-1AG40-0XB0	CPU 1215C, DC/DC/DC	14/10	Transistor	24 Vdc
862-4496	6ES7215-1HG40-0XB0	CPU 1215C, DC/DC/Relay	14/10	Relay	24 Vdc
862-4499	6ES7217-1AG40-0XB0	CPU 1217C, DC/DC/DC	14/10	Transistor	24 Vdc



### Starter Kits

Stock-No.	Siemens-MPN	Description
770-4308	6ES7212-1BD34-4YB0	Starter Kit S7-1200 + Software + Accessories
864-4002	6AV6651-7HA01-3AA4	Starter Kit S7-1200 + KP300 + Software + Accessories
828-5259	6AV6651-7KA01-3AA4	Starter Kit S7-1200 + KTP400 + Software + Accessories
864-3999	6AV6651-7DA01-3AA4	Starter Kit S7-1200 + KTP700 + Software + Accessories



### Accessories

Stock-No.	Description
746-5760	Signal Board SB1221, 4 digital input - More versions online
787-7942	Signal Module SM1221, 8 digital input - More versions online
735-2904	Communication Board CB1241, RS485
810-4166	Communication Module CM1241, RS422/RS485
810-4169	Communication Module CM1241, RS232
828-5268	SIMATIC STEP 7 Basic V13 Software
828-5256	Micro SD Card for SIMATIC S7-1200 Series CPU
668-3137	Simulator Module, 8 Channel Input Switches
208-3568	Simulator Module, 14 Channel Input Switches
668-0554	SITOP Power Supply 60W Switch Mode DIN Rail Mount, 24Vdc, 2.5A



For more technical information please visit:

[www.rs-online.com](http://www.rs-online.com)