

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348992020](#)
Status: **Active**
Overview: MXP120™ Sealed Connector System
Description: MXP120™ Sealed Male Blade Connector with 7.00mm Clip-Slot, 2 Circuit, Black Housing, Key A

Documents:

| | |
|---|--|
| 3D Model | Application Specification AS-34900-0001-CH (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-34900-0001 (PDF) | Product Literature (PDF) |

General

| | |
|-----------------------------|---|
| Product Family | Crimp Housings |
| Series | 34899 |
| Application | Sealed, Wire-to-Wire |
| Comments | See sales drawing for terminal information. |
| Overview | MXP120™ Sealed Connector System |
| Polarization | A |
| Product Literature Order No | 987650-7994 |
| Product Name | MXP120™ Sealed |
| UPC | 887191680415 |

Physical

| | |
|-------------------------------|-----------------|
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Gender | Male |
| Glow-Wire Compliant | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | SPS/Nylon |
| Net Weight | 3.500/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 4.00mm |
| Pitch - Termination Interface | 4.00mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40°C to +125°C |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 13.0A |
|-------------------------------|-------|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|------------------|
| Application Specification | AS-34900-0001-CH |
| Product Specification | PS-34900-0001 |
| Sales Drawing | SD-34899-2001 |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/39/2015 (15 June
2015)

Halogen-Free

Status

Not Relevant

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

Search Parts in this Series

[34899 Series](#)

Mates With

MXP120™ Female Receptacle [34900-2120](#)

Use With

1.2 CB SWS from Tyco