

LEDLENSER iXEO19R Rechargeable

The phenomenal iXEO19R from Ledlenser is an industrial-strength rechargeable multi-use handheld torch/headlamp that will effortlessly light up a railway tunnel, telegraph pylon, or even an entire worksite area. With its sensational 2000 lumen white light that can easily beam out to 300 meters, the XEO19R is a truly stunning piece of kit that will chase the darkness away and make life easier for professionals where a reliably powerful work light is essential. Its incredible performance comes from two frontal premium LEDs, each of which can be operated independently or together, via X-Lens Technology™, to form a single shatteringly-strong beam of even bright white light. The light is so strong that the iXEO19R even features its own thermal Speed Cooling System™ which results in the LEDs being cooled by an inflow of air resulting in a brighter light the faster the user travels - especially useful when on bicycles or motorised vehicles out in open environments. Light quality is astounding because the iXEO19R incorporates the patented Advanced Focus System®, which combines lens and reflector system to ensure powerful unbroken light from long-distance flood to near-view spot beam. The impressive Smart Light Technology™ feature offers 6 different light functions for any situation: Boost, Low Power, Power, Opti-Sense™ (Auto-dim), Strobe and an Emergency (10 lumen) light. There is a choice of Energy Saving or Constant Current light management programmes to help conserve power (and thus optimise light duration) or boost light intensity as and when required. Surprisingly easy to master, the iXEO19R has a front switch to control the light functions, Speed Focus™ to operate the two lenses and a power box with integrated charging status display. The XEO19R is supplied with a host of attachments and accessories that help make this light the perfect all-rounder for work or leisure. Especially useful is a helmet mount kit and a tri-pod mount to help affix the light to a tripod for use as an Area Light. As a rechargeable light the iXEO19R is more energy efficient and better for the environment. The newly developed 5200mAh battery pack also doubles as a handy power pack thus enabling charging of mobile phones, cameras or any item that needs charging via a USB point. Very handy when no other option is available. For additional convenience charging of these items can take place whilst the light is in use. The XEO19R is rated IPX6 for superior dust and water protection. An activation lock to prevent accidental battery discharge smartly round off this unique light.

- Dual focus rechargeable hands-free mega-light with 2 x Premium LEDs
- 5 in 1 use – Handheld Torch, Headlamp, Helmet Light, Area Light, Emergency Light
- X Lens Technology™ - two separate reflector lenses with independent focusing
- Smart Light Technology™ (SLT) - Boost, Low Power, Power, Opti-Sense™ (automatic dim), Strobe, Emergency
- Advanced Focus System™ (AFS) - Flood Beam to Sharply Focused Spot Beam
- Opti-Sense™ Active Light Measurement Technology - automatically adjusts light output to suit surroundings thus preserving battery life
- Thermal Speed Cooling System™ - better LED cooling when user is traveling at speed resulting in a brighter light output
- Lithium-ion Rechargeable Battery/Power Pack incorporating handy USB port for accessory charging
- Lamp head swivels for directional light
- Transport Lock – prevents light accidentally switching on and thus accidental battery drain.
- Charging status display and low battery warning indicator
- IPX6 – superior dust and water protection
- Supplied with: Helmet Mount Kit, Tripod Mount, GoPro® Accessories Mount, Waist-clip for battery power pack, L-ion battery power pack, Adaptor short cable, Extension cable, Neoprene pouch for battery box

Technical Information

iXEO19R	BOOST	POWER	LOW POWER	EMERGENCY
POWER	2000 lumens	1000 lumens	200 lumens	10 lumens
BEAM DISTANCE	300 metres	220 metres	100 metres	x
RUN TIME	4 hours	8 hours	20 hours	400 hours
SIZE	x		WEIGHT	478g

Supplied with: Helmet Mount Kit, Tripod Mount, GoPro® Accessories Mount, Waist-clip for battery power pack, L-ion battery power pack, Adaptor short cable, Extension cable, Neoprene pouch for battery box



Code	Description	Unit Colour	Packaging	Barcode
5619R	iXEO19R	Black/Yellow	Softcase	4029113561907