



ENGLISH

Datasheet

RS Pro 352 piece Bright Zinc Plated Steel Imperial Clevis Pin Kit

RS Stock No: **279-492**



Product Details

RS Pro 352-piece imperial clevis pin kit includes both pins and clips and is supplied in a plastic compartment storage box. Full dimensional data is also supplied with the kit. The clevis pin and retaining clip is made from mild steel and is bright zinc plated for corrosion resistance.

Features and Benefits

- Diameter ranging from 3/16 to 3/8 Inch
- Length ranging from 1/2 to 1-1/2 Inch
- Clevis, retaining clip
- Imperial system of measurement




Specifications:

Diameter Largest	3/8 in
Diameter Smallest	3/16 in
Finish	Bright Zinc Plated
Length Longest	1-1/2 in
Length Shortest	1/2 in
Material	Steel
Number of Pieces	352
Pin Type	Clevis, Retaining Clip
System of Measurement	Imperial

Imperial Clevis Pin Kit

Stock No. 279-492

D	D2	A	M	t
3/16	5/16	0.145	0.07	1/6
1/4	3/8	0.176	0.07	3/32
5/16	7/16	0.224	0.104	3/32
3/8	1/2	0.250	0.104	1/8



<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/16 x 1/2in</td> <td></td> <td>20</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/16 x 1/2in		20	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/16 x 5/8in</td> <td></td> <td>20</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/16 x 5/8in		20	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/16 x 3/4in</td> <td></td> <td>15</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/16 x 3/4in		15	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/16 x 1in</td> <td></td> <td>15</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/16 x 1in		15	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>1/4 x 3/4in</td> <td></td> <td>15</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	1/4 x 3/4in		15	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>1/4 x 1in</td> <td></td> <td>15</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	1/4 x 1in		15
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/16 x 1/2in		20																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/16 x 5/8in		20																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/16 x 3/4in		15																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/16 x 1in		15																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
1/4 x 3/4in		15																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
1/4 x 1in		15																																																									
<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>1/4 x 1 1/4in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	1/4 x 1 1/4in		10	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>1/4 x 1 1/2in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	1/4 x 1 1/2in		10	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>5/16 x 1in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	5/16 x 1in		10	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>5/16 x 1 1/4in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	5/16 x 1 1/4in		10	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>5/16 x 1 1/2in</td> <td></td> <td>8</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	5/16 x 1 1/2in		8	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/8 x 1in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/8 x 1in		10
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
1/4 x 1 1/4in		10																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
1/4 x 1 1/2in		10																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
5/16 x 1in		10																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
5/16 x 1 1/4in		10																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
5/16 x 1 1/2in		8																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/8 x 1in		10																																																									
<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/8 x 1 1/4in</td> <td></td> <td>10</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/8 x 1 1/4in		10	<table border="1"> <thead> <tr> <th colspan="3">Clevis Pins</th> </tr> <tr> <th>Dia.</th> <th>Length</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/8 x 1 1/2in</td> <td></td> <td>8</td> </tr> </tbody> </table>	Clevis Pins			Dia.	Length	Qty.	3/8 x 1 1/2in		8	<table border="1"> <thead> <tr> <th colspan="2">Retaining Clip</th> </tr> <tr> <th>Size</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/16in</td> <td>70</td> </tr> </tbody> </table>	Retaining Clip		Size	Qty.	3/16in	70	<table border="1"> <thead> <tr> <th colspan="2">Retaining Clip</th> </tr> <tr> <th>Size</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>1/4in</td> <td>50</td> </tr> </tbody> </table>	Retaining Clip		Size	Qty.	1/4in	50	<table border="1"> <thead> <tr> <th colspan="2">Retaining Clip</th> </tr> <tr> <th>Size</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>5/16in</td> <td>50</td> </tr> </tbody> </table>	Retaining Clip		Size	Qty.	5/16in	50	<table border="1"> <thead> <tr> <th colspan="2">Retaining Clip</th> </tr> <tr> <th>Size</th> <th>Qty.</th> </tr> </thead> <tbody> <tr> <td>3/8in</td> <td>28</td> </tr> </tbody> </table>	Retaining Clip		Size	Qty.	3/8in	28												
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/8 x 1 1/4in		10																																																									
Clevis Pins																																																											
Dia.	Length	Qty.																																																									
3/8 x 1 1/2in		8																																																									
Retaining Clip																																																											
Size	Qty.																																																										
3/16in	70																																																										
Retaining Clip																																																											
Size	Qty.																																																										
1/4in	50																																																										
Retaining Clip																																																											
Size	Qty.																																																										
5/16in	50																																																										
Retaining Clip																																																											
Size	Qty.																																																										
3/8in	28																																																										