

# PV-CAP-M



Products Low Voltage Products and Systems Connection Devices Photovoltaic Connectors Accessories for PV Connectors

## General Information

<b>Extended Product Type:</b>	PV-CAP-M
<b>Product ID:</b>	1SNV420174R0000
<b>EAN:</b>	3472599854574
<b>Catalog Description:</b>	PV-CAP-M - MC4-Evo2 PV accessories - Male - Sealing cap - PKG 100
<b>Long Description:</b>	- Unmated connectors must be protected from moisture and dirt with a sealing cap, - Full compatibility with all Multi-Contact MC4 family products, - Use the tools specified by ABB and Multi-Contact to guarantee the connection quality and reliability, - User manual MA 258.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation 105 °C Storage -40 ... +85 °C
<b>Ambient Temperature:</b>	-40 ... +85 °C
<b>Color:</b>	Black
<b>Country of Origin:</b>	Germany (DE)
<b>Customs Tariff Number:</b>	39235090
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP67
<b>EAN:</b>	3472599854574
<b>Function:</b>	Sealing cap
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Insulation Material:</b>	TPE
<b>Invoice Description:</b>	PV-CAP-M - MC4-Evo2 PV accessories - Male - Sealing cap - PKG 100
<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 1500 V
<b>Minimum Order Quantity:</b>	100 piece
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	100 piece
<b>Package Level 1 EAN:</b>	3472599854574
<b>Package Level 1 Gross Weight:</b>	0.28 kg
<b>Package Level 1 Height:</b>	100 mm
<b>Package Level 1 Length:</b>	175 mm
<b>Package Level 1 Units:</b>	100 piece
<b>Package Level 1 Width:</b>	115 mm
<b>Package Level 2 Height:</b>	125 mm
<b>Package Level 2 Length:</b>	300 mm
<b>Package Level 2 Units:</b>	200 piece
<b>Package Level 2 Width:</b>	200 mm
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	PV-CAP-M
<b>Product Name:</b>	MC4-Evo2 PV sealing cap
<b>Product Net Height:</b>	19 mm
<b>Product Net Weight:</b>	2.8 g
<b>Product Net Width:</b>	19 mm
<b>Product Packing Type:</b>	Bag
<b>Rated Voltage (U<sub>r</sub>):</b>	1500 V
<b>RoHS Information:</b>	1SND230569F0200
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	PV-CAP-M
<b>Sub-Function:</b>	For unmated male connectors