

tesa® 60632

Conformable aluminum tape with paper liner - 30µ foil

tesa® 60632 is a conformable aluminum tape based on a 30 µm (1.2 mil) aluminum foil, a transparent acrylic adhesive and a white, single-sided siliconized, 85µm thick paper liner

Features:

- Conformable to curved surfaces
- Easily removable liner
- Suitable for permanent applications
- Barrier against moisture, gases and vapors
- Electrically and thermally conductive
- Aging resistant
- Heat and light reflective
- Flame retardant according to DIN 4102, class B1
- Flame retardant according to the requirements in UL 510A

Main Application

- Mounting of refrigerator coils in appliance industry
- Joining and sealing of thermal insulation and ducts
- To make substrates electrically and thermally conductive
- To reflect heat radiation

Technical Data

▪ Backing material	aluminium foil	▪ Thickness of liner	85 µm
▪ Total thickness	65 µm	▪ Release of liner	easy
▪ Type of adhesive	acrylic	▪ Temperature resistance min.	-40 °C
▪ Adhesion to steel	8 N/cm	▪ Temperature resistance max.	160 °C
▪ Elongation at break	3 %	▪ Surface finish	reflective
▪ Tensile strength	25 N/cm		

Adhesion to

▪ Glass (initial)	8.0 N/cm	▪ PVC (initial)	5.5 N/cm
▪ PE (initial)	4.0 N/cm		

Properties

▪ Hand tearability	●●●●	▪ Abrasion resistance	●●●●
▪ Suitable for die cutting	yes	▪ Water resistance	●●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=60632>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

tesa® 60632

Conformable aluminum tape with paper liner - 30µ foil

Additional Information

The total thickness given in the section "Technical Data" describes the thickness of the tape without liner. The thickness with liner is 150 µm (5.9 mil).

For latest information on this product please visit <http://l.tesa.com/?ip=60632>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

