

SAFETY DATA SHEET

Goodfellow

Machineable Glass Ceramic

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : Machineable Glass Ceramic
Product code : MA800
Product type : Solid.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

1.3 Details of the supplier of the safety data sheet

Goodfellow Cambridge Limited
Ermine Business Park, Huntingdon, England PE29 6WR
Telephone: 0800 731 4653 (UK) or +44 1480 424 800
Fax: 0800 328 7689 (UK) or +44 1480 424 900

e-mail address of person responsible for this SDS : sds@goodfellow.com

1.4 Emergency telephone number

Telephone number : Chemtrec +1 202 483 7616

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

Ingredients of unknown toxicity : Percentage of the mixture consisting of ingredient(s) of unknown toxicity: 93%

Ingredients of unknown ecotoxicity : Percentage of the mixture consisting of ingredient(s) of unknown hazards to the aquatic environment: 83%

Classification according to Directive 1999/45/EC [DPD]

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : Not classified.

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Hazard pictograms :

Signal word : No signal word.

Hazard statements : No known significant effects or critical hazards.

Precautionary statements

Prevention : Not applicable.

Response : Not applicable.

Storage : Not applicable.

Disposal : Not applicable.

2.3 Other hazards

Avoid inhalation of and contact with eyes by any dust produced during machining, cutting or processing (a safety data sheet for product in powder form is available on request).

Machineable Glass Ceramic

SECTION 2: Hazards identification

Other hazards which do not result in classification : None known.

SECTION 3: Composition/information on ingredients

Substance/mixture : Mixture

| Product/ingredient name | Identifiers | % | Classification | | Type |
|----------------------------|----------------------------------|---------------|-----------------|-------------------------------------|------|
| | | | 67/548/EEC | Regulation (EC) No. 1272/2008 [CLP] | |
| Quartz (SiO ₂) | EC: 238-878-4 CAS: 14808-60-7 | >=35 - <50 | Not classified. | Not classified. | [2] |
| magnesium oxide | EC: 215-171-9 CAS: 1309-48-4 | >=15 - <20 | Not classified. | Not classified. | [2] |
| aluminium oxide | EC: 215-691-6 CAS: 1344-28-1 | >=15 - <20 | Not classified. | Not classified. | [2] |
| Fluoride | CAS: 16984-48-8 | >=1 - <5 | Not classified. | Not classified. | [2] |

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs or vPvBs or have been assigned a workplace exposure limit and hence require reporting in this section.

Type

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

[3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII

[4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

SECTION 4: First aid measures

4.1 Description of first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

4.2 Most important symptoms and effects, both acute and delayed

Potential acute health effects

No known significant effects or critical hazards.

Over-exposure signs/symptoms

No specific data.

4.3 Indication of any immediate medical attention and special treatment needed

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

SECTION 4: First aid measures

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use an extinguishing agent suitable for the surrounding fire.

5.2 Special hazards arising from the substance or mixture

Hazards from the substance or mixture : No specific fire or explosion hazard.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
halogenated compounds
metal oxide/oxides

5.3 Advice for firefighters

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials.

6.2 Environmental precautions

: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

6.3 Methods and materials for containment and cleaning up

Small spill : Move containers from spill area. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

Large spill : Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

6.4 Reference to other sections

: See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

7.1 Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

7.2 Conditions for safe storage, including any incompatibilities

- : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

8.1 Control parameters

Occupational exposure limits

| Product/ingredient name | Exposure limit values |
|----------------------------|---|
| Quartz (SiO ₂) | EH40/2005 WELs (United Kingdom (UK), 8/2007). TWA: 0.1 mg/m ³ 8 hours. Form: respirable dust |
| magnesium oxide | EH40/2005 WELs (United Kingdom (UK), 8/2007). TWA: 10 mg/m ³ , (as Mg) 8 hours. Form: inhalable dust TWA: 4 mg/m ³ , (as Mg) 8 hours. Form: respirable dust and fume |
| aluminium oxide | EH40/2005 WELs (United Kingdom (UK), 8/2007). TWA: 10 mg/m ³ 8 hours. Form: inhalable dust |
| Fluoride | EH40/2005 WELs (United Kingdom (UK), 8/2007). TWA: 2.5 mg/m ³ , (as F) 8 hours. |

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

8.2 Exposure controls

- Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

SECTION 8: Exposure controls/personal protection

- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Use a properly fitted, particulate filter respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

- Physical state** : Solid.
- Colour** : Not available.
- Odour** : Not available.

SECTION 10: Stability and reactivity

- 10.1 Reactivity** : No specific test data related to reactivity available for this product or its ingredients.
- 10.2 Chemical stability** : The product is stable.
- 10.3 Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.
- 10.4 Conditions to avoid** : No specific data.
- 10.5 Incompatible materials** : No specific data.
- 10.6 Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

- Conclusion/Summary** : Not available.

Acute toxicity estimates

Not available.

Irritation/Corrosion

SECTION 11: Toxicological information

Conclusion/Summary : Not available.

Sensitisation

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on the likely routes of exposure : Not available.

Potential acute health effects

No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Not available.

Potential chronic health effects

Conclusion/Summary : Not available.

General : No known significant effects or critical hazards.

Carcinogenicity : No known significant effects or critical hazards.

Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : No known significant effects or critical hazards.

Developmental effects : No known significant effects or critical hazards.

Fertility effects : No known significant effects or critical hazards.

Other information : Not available.

SECTION 12: Ecological information**12.1 Toxicity**

Conclusion/Summary : Not available.

12.2 Persistence and degradability

Conclusion/Summary : Not available.

12.3 Bioaccumulative potential

Not available.

12.4 Mobility in soil

Machineable Glass Ceramic

SECTION 12: Ecological information

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

: Not applicable.

12.6 Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

| | ADR/RID | ADN | IMDG | IATA |
|-----------------------|----------------|----------------|----------------|----------------|
| 14.1 UN number | Not available. | Not available. | Not available. | Not available. |

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Regulation (EC) No. 1907/2006 (REACH)

Annex XIV - List of substances subject to authorisation

Substances of very high concern

None of the components are listed.

SECTION 15: Regulatory information

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles : Not applicable.

Other EU regulations

Europe inventory : Not determined.

Black List Chemicals : Not listed

Priority List Chemicals : Not listed

Integrated pollution prevention and control list (IPPC) - Air : Listed

Integrated pollution prevention and control list (IPPC) - Water : Not listed

International regulations

15.2 Chemical Safety Assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

Abbreviations and acronyms : ATE = Acute Toxicity Estimate
 CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
 DNEL = Derived No Effect Level
 EUH statement = CLP-specific Hazard statement
 PNEC = Predicted No Effect Concentration
 RRN = REACH Registration Number

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

| Classification | Justification |
|-----------------|---------------|
| Not classified. | |

Full text of abbreviated H statements : Not applicable.

Full text of classifications [CLP/GHS] : Not applicable.

Full text of abbreviated R phrases : Not applicable.

Full text of classifications [DSD/DPD] : Not applicable.

Date of issue/ Date of revision : 2015,01,06.

Date of previous issue : 2015,01,06.

Version : 9

Notice to reader

Further information.

License granted to make unlimited paper copies for internal use only.

This datasheet has been compiled for guidance in connection with products sourced from and supplied by Metals & Materials Limited only, including all subsidiary companies (Goodfellow Cambridge Limited, Goodfellow SARL, Goodfellow GmbH, Goodfellow Corporation and Goodfellow (Shanghai) Trading Co., Ltd., subsequently referred to as "Goodfellow") and must not be used in connection with any non-Goodfellow supplied products. In accepting receipt of this datasheet with no material purchase from Goodfellow, you agree to absolve Goodfellow entirely and waive any legal rights or remedy against Goodfellow arising from such unauthorised use

SECTION 16: Other information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. It is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. Employers should use this information only as a supplement to other information gathered by them and should make independent judgement of the suitability of this information to ensure proper use of the product and to protect the health and safety of their employees and the end-user(s) of the product.

Goodfellow supplies this information without warranty and any use of the product not in conformance with this Material Safety Data Sheet or in combination with any other product or process is the responsibility of the user. The Company does not represent any guarantee of the properties of the product or any suitability of the product for a given application.

Goodfellow shall not be held liable for any damage resulting from handling or from contact with the product. See www.goodfellow.com or www.goodfellowusa.com for additional terms and conditions of sale.

Copyright 2010 - 2015 Metals & Materials Limited