

TEST/CHARACTERISTICS	STANDARD REFERENCE	VALUES/REMARKS		
----------------------	--------------------	----------------	--	--

ELECTRICAL CHARACTERISTICS

Impedance		50 Ω		
Frequency range		DC-4 GHz		
Typical V.S.W.R. <i>Straight models cable group : 2/50, 2.6/50, 5/50, 10 + 11/50, .141"</i> <i>Right angle models 2/50, 2.6/50, 5/50,</i>		1 GHz 1.12	2.5 GHz 1.18 1.30 max	4 GHz 1.22
Insertion loss <i>straight connector</i> <i>right-angle connector</i>		0.05 0.08	0.07 0.16	0.13 0.20
RF Leakage		- 55 dB min from 2 to 3 GHz		
Insulation resistance		5000 MΩ min	5000 MΩ min	5000 MΩ min
Contact resistance <i>center contact</i> <i>outer contact</i>	MIL	1.5 mΩ 0.2 mΩ		
Working voltage in VRMS <i>at sea level</i> <i>(at 21 000m)</i>		500 125		
Dielectric withstanding voltage in VRMS <i>at sea level</i> <i>(at 21 000m)</i>		1500 375		
RF testing voltage in VRMS <i>sea level (5 MHz)</i>		1000		

MECHANICAL CHARACTERISTICS


Durability		500 matings		
Force to engage and disengage <i>axial</i> <i>torque</i>		13.6 N max 28.6 Ncm		
Coupling nut retention force	MIL	445 N		
Cable retention force <i>cable 2/50, 2.6/50</i> <i>cable 5/50, 10 + 11/50</i> <i>cable .141"</i>		227 N		
Center contact retention force		27.2 N		

ENVIRONMENTAL CHARACTERISTICS

Temperature range <i>flexible cables</i> <i>semi-rigid cables</i>	MIL	- 65°C + 165°C - 65°C + 105°C		
Thermo cycling test		MIL STD 202, method 107, condition B		
Thermal shock		MIL STD 202, method 107, condition B		
Hight temperature endurance		MIL STD 202, method 108		
Corrosion salt spray		MIL STD 202, method 101, condition B		
Vibration		MIL STD 202, method 204, condition B		
Shock		MIL STD 202, method 213, condition G		
Moisture resistance		MIL STD 202, method 106		
Hermetic test		MIL STD 202, method 112, condition C vacuum 10 ⁻⁶ Hgmm (Torr) leakage rate < 10 ⁻⁶ atm/cm ³ /s		
Barometric pressure		Pressure test : 3.5 bars; duration : 2 mn; temperature : 15° C to 25 °C		

BNC 50 Ω

CHARACTERISTICS




MATERIALS

Bodies		Brass
Center contact	<i>male</i> <i>female</i>	Brass Bronze or heat treated beryllium following QQ-C-530
Nut		Brass
Insulator		PTFE
Gasket		Silicon rubber

PLATINGS


Bodies		Nickel
Center contacts		Gold

POWER RATING



Standard packaging : unit

All dimensions are given in mm.



TEST/CHARACTERISTICS	STANDARD REFERENCE	VALUES/REMARKS
----------------------	--------------------	----------------

ELECTRICAL CHARACTERISTICS

Impedance		75 Ω
Frequency range		DC-1 GHz
V.S.W.R. max <i>Straight models cable group : 2.6/75, 5/75, 6/75, 8/75, 10 + 11/75</i> <i>Right angle models 2.6/75, 6/75</i>		1.30 1.35
Insertion loss <i>straight connector</i> <i>right-angle connector</i>		0.2 dB max at 1 GHz 0.3 dB max at 1 GHz
RF Leakage		- 55 dB min from 2 to 3 GHz
Insulation resistance		5000 MΩ min
Contact resistance <i>center contact</i> <i>outer contact</i>	MIL	1.5 mΩ 0.2 mΩ
Working voltage in VRMS <i>at sea level</i> <i>(at 21 000m)</i>		500 125
Dielectric withstanding voltage in VRMS <i>at sea level</i> <i>(at 21 000m)</i>		1500 375
RF testing voltage in VRMS <i>sea level (5 MHz)</i>		1000

MECHANICAL CHARACTERISTICS

Durability		500 matings
Force to engage and disengage <i>axial</i> <i>torque</i>		13.6 N max 28.6 Ncm
Coupling nut retention force	MIL	445 N
Cable retention force <i>cable 2.6/75, 5/75, 6/75, 8/75, 10 + 11/75</i>		340 N
Center contact retention force		

ENVIRONMENTAL CHARACTERISTICS

Temperature range <i>flexible cables</i>	MIL	- 65°C + 165°C
Thermo cycling test		MIL STD 202, method 107, condition B
Thermal shock		
High temperature endurance		MIL STD 202, method 108
Corrosion salt spray		MIL STD 202, method 101, condition B
Vibration		MIL STD 202, method 204, condition B
Shock		MIL STD 202, method 213, condition G
Moisture resistance		MIL STD 202, method 106
Hermetic test		MIL STD 202, method 112, condition C vacuum 10 ⁻⁶ Hgmm (Torr) leakage rate < 10 ⁻⁶ atm/cm ³ /s
Barometric pressure		Pressure test : 3.5 bars; duration : 2 mn; temperature : 15° C to 25 °C

MATERIALS


Bodies		Brass
Center contact <i>male</i> <i>female</i>		Brass Bronze or heat treated beryllium following QQ-C-530
Nut		Brass
Insulator		PTFE
Gasket		Silicon rubber

PLATINGS


Bodies		Nickel
Center contacts		Gold

Standard packaging : unit

All dimensions are given in mm.




RESISTIVE PADS (500W peak)



Part number	Frequency Range	Technical design	Impedance (Ω)	Type	Weight (g)
R404 412 000	DC – 1 GHz	Resistive PAD	75 \pm 0.1%	M	15
R404 441 000			50 \pm 1%		
R404 442 000			75 \pm 1%		

LOW POWER TERMINATIONS (500W peak)



Part number	Freq. Range (GHz)	V.S.W.R. (max)					Power (W) Avg.	Impedance (Ω)	Type	Dimensions (mm)		Weight (g)
		DC-0.5	0.5-1	1-2.5	2.5-4	4-8				A	B	
R404 011 000	DC – 1	1.08	1.15				1	50 \pm 2%	M	31	14.5	15
R404 013 000								F	29	11		
R404 012 000								M	31	14.5		
R404 014 000								F	29	11		
R404 111 000	DC – 2.5	1.08	1.20			50 \pm 2%		M	31	14.5		
R404 112 000						F		29	11			
R404 110 000	DC – 8	1.10			1.20	1.25		50 \pm 5%	M	31	14.5	