

PRODUCT GROUP 1053B

BOLT CLAMPS

Construction



Bolt clamps are constructed from low carbon mild steel and finished with a zinc-plating. Stainless steel clamps of the same design can be made to order. Each clip has its range stamped in millimetres on the band, for ease of identification.

Applications

Bolt clamps are a stronger alternative to wormdrive clips, able to withstand greater pressures, whilst being completely reusable. They can be used for the secure attachment of fittings to many types of hose, including P.V.C. rubber, silicone etc.

Sizes available (mm)

Diameter Range d	Band Width w	Total Width t	Metal Thickness (band) b	Total Overall Dimensions D		Recomm. Applic. Torque Nm	Recomm. Working Pressure Bar
				min	max.		
17-19	18.0	19.8	0.6	29	31	3.5	34
20-22	18.0	19.8	0.6	32	34	3.5	34
23-25	18.0	19.8	0.6	35	37	3.5	34
26-28	18.0	19.8	0.6	38	40	3.5	34
29-31	20.0	22.0	0.8	42	44	6.0	30
32-35	20.0	22.0	0.8	45	48	6.0	30
36-39	20.0	22.0	0.8	49	52	6.0	30
40-43	20.0	22.0	0.8	53	56	6.0	30
44-47	22.0	24.5	1.2	60	63	12.0	35
48-51	22.0	24.5	1.2	64	67	12.0	35
52-55	22.0	24.5	1.2	68	71	12.0	35
56-59	22.0	24.5	1.2	72	75	12.0	29
60-63	22.0	24.5	1.2	76	79	12.0	29
64-67	22.0	24.5	1.2	80	83	12.0	29
68-73	24.0	26.5	1.5	86	91	19.0	22
74-79	24.0	26.5	1.5	92	97	19.0	22
80-85	24.0	26.5	1.5	98	103	19.0	22
86-91	24.0	26.5	1.5	104	109	19.0	16
92-97	24.0	26.5	1.5	110	115	19.0	16
98-103	24.0	26.5	1.5	116	121	19.0	16
104-112	24.0	26.5	1.5	122	130	19.0	10
113-121	24.0	26.5	1.5	131	139	19.0	10
122-130	24.0	26.5	1.5	140	148	19.0	10
131-139	26.0	29.0	1.7	152	160	37.5	7
140-148	26.0	29.0	1.7	161	169	37.5	7
149-161	26.0	29.0	1.7	170	182	37.5	7
162-174	26.0	29.0	1.7	183	195	37.5	5
175-187	26.0	29.0	1.7	196	208	37.5	5
188-200	26.0	29.0	1.7	209	221	37.5	5
201-213	26.0	29.0	1.7	222	234	37.5	2
214-226	26.0	29.0	1.7	235	247	37.5	2
227-239	26.0	29.0	1.7	248	260	37.5	2
240-252	26.0	29.0	1.7	261	273	37.5	2



For details of wormdrive clips see leaflet WD610 and for 'O' clips see leaflet WD630.

Important Note: Please note that the information is to the best of our knowledge, true and accurate. We reserve the right to alter the specifications without notice. Since conditions under which the products may be used are beyond our control, our recommendations are made without warranty or guarantee and we cannot be held responsible for misuse of products or information. However, our experienced technical staff would be happy to advise you on the uses for which our products are suitable.

Southern Division & Headquarters:
FLEXIBLE HOSE SUPPLIES LTD.,
140 EDINBURGH AVENUE,
SLOUGH, BERKS, SL1 4UA
TEL: 01753 570863
FAX: 01753 824141
TELEX: 849182

Midland Division & Manufacturing Plant:
FLEX-METALLIC INDUSTRIES,
CASWELL ROAD, BRACKMILLS INDUSTRIAL ESTATE,
NORTHAMPTON, NN4
TEL: 01604 762175
FAX: 01604 769915

Northern Division:
FLEXIBLE HOSE SUPPLIES LTD.,
SPRINGFIELD ROAD, KEARSLEY,
BOLTON, LANCs, BL4 8NB
TEL: 01204 795735
FAX: 01204 795767