



CUSTOM POWER DESIGN

ELECTRONICS CONSULTANTS PROVIDING CUSTOM DESIGN, DEVELOPMENT, TEST & SUPPORT



Tel: + 44 (0)118 930 2113/2299

A DIVISION OF SMET LTD

Fax: +44 (0)118 930 2206

www.custompowerdesign.co.uk

Unit 2, The Markham Centre, Station Road, Theale, Berks. RG7 4PE.

custom@custompowerdesign.co.uk

BATTERY TO MAINS ADAPTORS FOR COMPUTER/CAMCORDER CHARGERS.

SM 2910 12V input, 3 PIN IEC C5 Lead.

SM 2911 12V input, IEC (kettle type) Lead.

SM 2919 12V input, Cassette (fig of '8') Lead.

SM 2912 24V input, 3 PIN IEC C5 Lead.

SM 2913 24V input, IEC (kettle type) Lead.

SM 2914 24V input, Cassette (fig of '8') Lead.



- PROVIDES MAINS POWER FOR OFFICE EQUIPMENT
- RUNS COMPUTER AND CAMCORDER CHARGERS
- HIGH OUTPUT POWER IN VERY COMPACT SIZE
- VERY HIGH CONVERSION EFFICIENCY

GENERAL DESCRIPTION

Small converters generating a mains level output from either a 12 or 24 volt car battery (depending on unit). The output is only suitable for powering equipment employing switched mode power conversion, where incoming AC mains is immediately rectified. This is true of most modern equipment especially computer and camcorder chargers.

Output is via a 1.5 metre cable ended socket depending on model. Small computer chargers usually use one of three types of mains connector. One is the common IEC (kettle) type, another is a 'figure of 8' cassette type and the last is the new 3 pin IEC C5 round type. Select the model with the correct lead from the list above.

Input is via a 0.6 metre lead terminated in a plug suitable for use with most cigar lighter fitments. Units with third wire on/off control, designed for permanent installation are available, call for details.

The Adaptor is fitted with an audible warning indicating that the battery is becoming discharged, prompting battery boost. Should the battery voltage fall below a critical level, the unit will switch off.

COMPATIBILITY CHECK: Measure the resistance between the live and neutral pins of the charger's mains connector

We reserve the right to change the specification without notice.

(no mains connected). If the resistance is greater than 10K ohms (no mains transformer primary) then the equipment should be compatible.

CAUTION: This adaptor is supplied on the basis of the user determining the suitability for the purpose for which it is to be used. Do not use in a moving vehicle without the consent of the vehicle manufacturer. Do not use for aviation or marine applications without our written agreement. Do not use for life dependent applications. The negative input lead is connected to case and output ground making the unit suitable only for negative earth systems. The output is only suitable for equipment employing switched mode power conversion, and not having a 50Hz mains transformer or mains heater element. The unit will not operate RCD Breakers.

SPECIFICATION:

INPUT

	12V TYPES.	24V TYPES.
Battery:	12V nominal.	24V nominal.
Voltage Range:	11V - 14.5V.	21.6V - 30V.
Current, No Load:	0.5A.	0.35A.
Per 10W loading:	1 A.	0.5A.
Battery Alarm:	10.5V.	20.7V.
Latch off level:	9.6V.	19V.

OUTPUT

Output Voltage:	230V AC equivalent Mains DC actually 330VDC nominal. For use with chargers using switched mode conversion only.
Capacitive load:	Unlimited.
Power, Nominal:	100 Watts continuous (resistive).
Power, Short term:	120 Watts for 1 minute.
Protection:	Current limit and battery fuse.

GENERAL

Size:	30mm x 111mm x 60mm. Weight: 0.4 Kg.
Storage Temperature:	-40 to +70C.
Operating Temperature:	-40 to +35C.
Manufacturer:	Made in the United Kingdom

Document 2911-993.