

# Product Information

## 2470PJP100P30

EAN 4031582010473

Swivel castor, housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, wheel axle with nut.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing, with threadguards, bolt hole

Castors can be mounted with standard screws; various length screws can be used..

Wheel diameter	100 mm
Width of Tread	32 mm
Centre hole	11 mm
Offset	38 mm
Swivel Interference	176 mm
Overall height	135 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.581 kg
Dynamic Load capacity	100 kg
Static Load capacity	200 kg
Swivel Radius	88 mm
Hardness of tread	A 87 Shore



### Versions:

