

# RAD-ISM-2400-ANT-OMNI-9-0

Order No.: 2867623

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867623>

Omni-directional antenna, IP65 degree of protection, 9 dBi gain, linear vertical, N (female) connection, impedance 50 ohms, apex angle h/v 360°/15°

**Commercial data**

EAN	4017918939007
Pack	1 Pcs.
Customs tariff	85177011
Weight/Piece	0.85 KG
Catalog page information	Page 524 (IF-2007)

**Product notes**

WEEE/RoHS-compliant since:  
09/03/2007



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

**Technical data****General data**

Horizontal beamwidth	360 °
Vertical beamwidth	15 °
Impedance	50 Ω
Gain	9 dBi

Type of connection	N (female)
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Width	25 mm
Height	625 mm

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford Shropshire TF7 4PG,GB  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



© 2008 Phoenix Contact  
Technical modifications reserved;