

QSiI553 (QSiI553) Thermally Conductive Silicone Encapsulant

Introduction

QSiI553 is a 2-component, silicone elastomer system specially designed for electronic potting applications. It offers good protection against impact damage and can be employed in areas where low flammability is a prerequisite. The cured product is a hard, medium to high modulus elastomer that can be repaired. The component parts have relatively low viscosities and are readily mixed in a simple 1:1 ratio.

Key Features

- **Thermally Conductive**
- **1:1 Mix ratio**
- **Moderately Low Viscosity**
- **Low Modulus**
- **UL(\$V) approved file No. E205830**

Use and Cure Information

How to Use

IMPORTANT: QSiI553 contains the platinum catalyst, great care should be taken when using automatic dispensing equipment. Please ensure that it is not contaminated by residual hydride containing rubber in the dispensing equipment, as curing will result. If in doubt, it's advised to thoroughly purge the equipment with a suitable hydrocarbon solvent or silicone fluid.

Mix both the A and B parts gently to ensure homogeneity. Place the required amount of A and B parts by weight at the ration of 1:1 (A to B) in a clean plastic or metal container of approximately 3 times their volume, and mix until the colour of the mixture is uniform. Degas by intermittent evacuation, the larger volume of the mixing vessel helps prevent overflow during this operation. In case of automatic dispensing with static mixing head, the two components should be degassed before processing. Recommended vacuum conditions are 30-50 mbar intermittently over 5-10 minutes. Cast the mixture either by gravity or pressure injection.

Curing Conditions

The following table offers a guide to the rate of cure of QSiI553 at various temperatures, mixing of the components between 15 and 25°C is recommended to ensure adequate pot life for degassing and handling. The pot life can be extended to several hours by chilling the components.

Temperature, °C	Max Cure Time
25	24 hrs
100	7 mins

Inhibition of Cure

Great care must be taken when handling and mixing all addition cured silicone elastomer systems, that all the mixing tools (vessels and spatulas) are clean and constructed in materials which do not interfere with the curing mechanism. The cure of the rubber can be inhibited by the presence of compounds of nitrogen, sulphur, phosphorus and arsenic; organotin catalysts and PVC stabilizers; epoxy resin catalysts and even contact with materials containing certain of these substances e.g. moulding clays, sulphur vulcanised rubbers, condensation cure silicone rubbers, onion and garlic.

Property	Test Method	Value
Uncured Product		
Colour A Part:		Beige
Colour B Part:		Black
Appearance:		Viscous Liquid
Viscosity A Part:	Brookfield	5000 mPa.s
Viscosity B Part:	Brookfield	3500 mPa.s
Catalysed viscosity	Brookfield	4500 mPa.s
Pot Life:		180 minutes *
SG 'A'Part		1.6
SG 'B'Part		1.6
* measured at 23+/-2°C and 65% relative humidity		

Cured Elastomer

(after 7 days cure at 23+/-2°C and 65% relative humidity)

Colour		Grey
Tensile Strength:	BS903 Part A2	1.20 MP
Elongation at Break:	BS903 Part A2	175 %
Youngs Modulus:		MPa
Modulus at 100% Strain:	BS903 Part A2	0.60 MPa
Hardness:	ASTM D 2240-95	32° Shore A
Specific Gravity:	BS 903 Part A1	1.6
Thermal Conductivity:		0.68 W/m
Coefficient of Thermal Expansion:		
Volumetric		650 ppm / °C
Linear		217 ppm / °C
Min. Service Temperature:		-55°C
Max. Service Temperature:	AFS 1540B	260 °C

Electrical Properties

Surface Resistivity

Volume Resistivity:	ASTM D-257	3.26E+14 Ω.cm
Dielectric Strength:	ASTM D-149	>18kV/mm
Dielectric Constant at 1 kHz:	ASTM D-150	3.41
Dissipation Factor	ASTM D-150	0.00496

Flammability

UL94 V-0 Rated **Yes**

Adhesion

Self-Bonding **No**

All values are typical and should not be accepted as a specification.

Health and Safety - Material Safety Data Sheets available on request.

Packages – ACC Addition encapsulants are supplied in a range of pack sizes please contact the sales office for details

Arrangements can be made to supply in other pack sizes.

Storage and Shelf Life – Expected to be 24 months in original, unopened containers below 30°C

Revision Date: 21/05/2013

The information and recommendations in this publication are to the best of our knowledge reliable. However nothing herein is to be construed as a warranty or representation. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.