

The Wiha Finish screwdriver concept.

The revolution in screwdriver design.

SoftFinish®



Wiha MicroFinish



Introducing the next generation of screwdrivers from Wiha: the SoftFinish® and the MicroFinish, because functionality and ergonomic styling together make up the most important aspect of a screwdriver.

The generation of Wiha Finish handles with its total of four handle sizes was developed on the basis of extensive studies into handle ergonomics with the support of high-profile research institutes. The result is a completely ergonomic design and optimal handle lengths and diameters. The user is guaranteed a perfect hold with every handle size.

The feel good factor

Due to the combination of material and handle size, each Finish screwdriver fits perfectly into the palm of the hand. There is no strain on muscles, ligaments and joints, with the result that minimum force is required for maximum torque.


SoftFinish® or MicroFinish

Screwdrivers used in dry working environments have to have a different handle surface to those used in oily working environments. Wiha has taken this on board and has developed a Finish screwdriver for dry and general applications and one for oily applications.

The handle core of both models consists of impact-resistant, recyclable special plastic material. The torque strengthening Finish zone of the SoftFinish® version is made of a soft, thermoplastic elastomer and is ideal for dry and general applications.

The Finish zone of the MicroFinish version is made of impact-resistant cellulose acetate that is also resistant to oil and chemicals. Its micro-fine surface structure ensures convincing high-torque transmission without slipping, even with oily hands.





Solid moulded core made of high-impact plastic material.

Large optimised handle diameter allows higher torque with less user hand fatigue.

Roll-off protection.

Reinforced connection between blade and moulded core.

SoftFinish® Zone for unbeatable comfort and maximum torque.

Round, smooth handle end.

Blade made of high quality chromevanadium- molybdenium steel, super hardened and chrome-plated for unmatched durability.

Wiha SoftFinish®.

The specialist for dry and general applications.



The right tool at a glance, thanks to the printed screw symbol on the handle end.

Blade with hex bolster for wrenches to use on particularly tight screws.

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum torque forces in dry and general working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.



Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.



Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time




Thermoplastic elastomer tolerates high loads and feels soft and pleasant to the touch.



► See VDE tools,
page 226 – 231

For slotted screws.




302 SoftFinish® slotted screwdriver.
Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 5265, DIN ISO 2380.
Application: Especially for dry and general applications.

Order-No.	⌀	↔	⊖	●	↔	↔	⊖	€ /pc.
00684 6	2.0	65	0.4	2.0	169	23	10	3.20
00685 3	2.5	75	0.4	2.5	179	23	10	3.45
00686 0	3.0	80	0.5	3.0	184	23	10	3.80
00687 7	3.0	100	0.5	3.0	204	23	10	4.00
00689 1	3.0	150	0.5	3.0	254	23	10	4.70
00690 7	3.0	200	0.5	3.0	304	23	10	5.50
32383 7	3.0	300	0.5	3.0	404	23	5	6.30
00691 4	3.5	100	0.6	3.5	204	23	10	3.90
26931 9	3.5	200	0.5	3.5	304	23	10	5.50
00692 1	4.0	100	0.8	4.0	211	30	10	4.60
00694 5	4.0	150	0.8	4.0	261	30	10	5.05
00695 2	4.0	200	0.8	4.0	311	30	10	5.05
00696 9	4.0	300	0.8	4.0	411	30	5	7.15
27753 6	4.5	80	0.8	4.5	191	30	10	4.65
00697 6	4.5	125	0.8	4.5	236	30	10	4.95
00698 3	5.5	125	1.0	5.5	236	30	10	7.05
00700 3	5.5	150	1.0	5.5	261	30	10	7.30
00701 0	5.5	200	1.0	5.5	311	30	10	7.90
00702 7	5.5	300	1.0	5.5	411	30	5	8.60
27754 3	6.0	100	1.2	6.0	218	36	10	7.50
27755 0	6.0	150	1.2	6.0	268	36	10	8.10
32384 4	6.0	300	1.1	6.0	418	36	5	8.80
00704 1	6.5	100	1.2	6.0	218	36	10	7.50
00703 4	6.5	150	1.2	6.0	268	36	10	8.10
00706 5	6.5	200	1.2	6.0	318	36	5	8.70
00708 9	8.0	150	1.2	7.0	274	41	10	10.10
00707 2	8.0	175	1.2	7.0	299	41	5	10.50
00709 6	8.0	175	1.6	7.0	299	41	5	10.50
32399 8	8.0	300	1.2	7.0	424	41	5	11.30
00711 9	10.0	200	1.6	8.0	324	41	5	13.10
32400 1	10.0	300	1.6	8.0	424	41	5	13.90
00712 6	12.0	250	2.0	8.0	374	41	5	16.60
00713 3	14.0	250	2.5	11.0	374	41	5	18.30

• Additional dimension. Non-DIN size.




308 SoftFinish® slotted screwdriver.
Hex blade with hex bolster.

Order-No.	⌀	↔	⊖	●	⊖	↔	↔	⊖	€ /pc.
00731 7	3.5	75	0.6	4.0	-	186	30	10	4.55
00732 4	4.5	90	0.8	4.0	-	201	30	10	5.80
00733 1	5.5	100	1.0	5.0	8	213	36	10	8.10
00734 8	6.5	125	1.2	6.0	10	238	36	10	8.80
00735 5	7.0	125	1.1	6.0	10	238	36	10	8.80
00736 2	8.0	150	1.2	8.0	13	268	41	10	11.60
00737 9	9.0	150	1.4	8.0	13	268	41	10	11.60
00738 6	10.0	175	1.6	8.0	13	293	41	5	14.00
00739 3	12.0	200	2.0	10.0	16	318	41	5	16.70
00740 9	14.0	250	2.5	10.0	16	368	41	5	19.30

• Additional dimension. Non-DIN size.

For slotted and Phillips screws.



530 SoftFinish® slotted screwdriver.
Hex blade with hex bolster, solid steel cap.

Order-No.	⌀	↔	⊖	●	⊖	↔	↔	⊖	€ /pc.
03223 4	3.5	75	0.6	4.0	-	186	30	10	7.60
03224 1	4.5	90	0.8	4.0	-	201	30	10	8.30
03225 8	5.5	100	1.0	5.0	8	213	36	10	10.60
03226 5	6.5	125	1.2	6.0	10	238	36	10	13.20
03228 9	8.0	150	1.2	8.0	13	271	41	5	17.80
03230 2	10.0	175	1.6	8.0	13	296	41	5	22.10
03231 9	12.0	200	2.0	10.0	16	321	41	5	28.10
03232 6	14.0	250	2.5	10.0	16	371	41	5	34.00

• Additional dimension. Non-DIN size.



NEW
398 SoftFinish® slotted screw-holding screwdriver.
Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Application: For setting and turning screws in difficult to access areas.

Order-No.	⌀	↔	⊖	↔	↔	⊖	€ /pc.
32867 2	2.5	75	0.4	186	30	5	12.40
32868 9	3.0	100	0.5	211	30	5	12.90
32869 6	4.0	125	0.8	243	36	5	15.80
32870 2	5.0	150	1.0	268	36	5	18.30
32871 9	6.0	175	1.2	293	36	5	20.50



311 SoftFinish® Phillips screwdriver.
Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	●	↔	↔	⊖	€ /pc.
00754 6	PH0	60	3.0	164	23	10	4.45
27756 7	PH0	100	3.0	204	23	10	4.95
00756 0	PH1	80	4.5	191	30	10	5.25
27757 4	PH1	100	4.5	211	30	10	5.80
00757 7	PH1	200	4.5	311	30	10	6.80
03738 3	PH1	300	4.5	411	30	5	7.80
00759 1	PH2	100	6.0	218	36	10	7.40
27758 1	PH2	150	6.0	268	36	10	8.20
00760 7	PH2	200	6.0	318	36	5	8.60
03739 0	PH2	300	6.0	418	36	5	9.60
00762 1	PH3	150	8.0	274	41	10	10.50
00763 8	PH4	200	10.0	324	41	5	14.10

• Additional dimension. Non-DIN size.

Wiha SoftFinish®.

The specialist for dry and general applications.

For Phillips screws.



312 SoftFinish® Phillips screwdriver. Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	⦿	⊖	↔	↔	↔	€/pc.
00764 5	PH1	80	5.0	8	186	30	10	6.40
00765 2	PH2	100	6.0	10	213	36	10	8.70
00766 9	PH3	150	8.0	13	268	41	10	12.30
00767 6	PH4	200	10.0	16	318	41	5	15.70



531 SoftFinish® Phillips screwdriver. Hex blade with hex bolster, solid steel cap.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	⦿	⊖	↔	↔	↔	€/pc.
03237 1	PH1	80	5.0	8	186	30	10	9.50
03238 8	PH2	100	6.0	10	213	36	10	13.40
03239 5	PH3	150	8.0	13	268	41	10	19.70



397 SoftFinish® Phillips screw-holding screwdriver. Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Application: For setting and turning screws in difficult to access areas.

Order-No.	⊕	↔	↔	↔	↔	€/pc.
32406 3	PH0	100	211	30		14.50
32404 9	PH1	125	236	36		17.40
32405 6	PH2	175	286	36		20.30

For Pozidriv screws.



313 SoftFinish® Pozidriv screwdriver. Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	⦿	⊖	↔	↔	↔	€/pc.
00768 3	PZ0	60	3.0	164	23		10	5.10
00770 6	PZ1	80	4.5	191	30		10	6.20
26454 3	PZ1	300	4.5	411	30		5	8.50
00772 0	PZ2	100	6.0	218	36		10	8.60
26455 0	PZ2	300	6.0	418	36		5	10.80
00774 4	PZ3	150	8.0	274	41		10	12.90



314 SoftFinish® Pozidriv screwdriver. Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	⦿	⊖	↔	↔	↔	€/pc.
00776 8	PZ1	80	5.0	8	186	30	10	8.00
00777 5	PZ2	100	6.0	10	213	36	10	10.40
00778 2	PZ3	150	8.0	13	268	41	10	15.10
00779 9	PZ4	200	10.0	16	318	41	5	19.10



532 SoftFinish® Pozidriv screwdriver. Hex blade with hex bolster, solid steel cap.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

Order-No.	⊕	↔	⦿	⊖	↔	↔	↔	€/pc.
03245 6	PZ1	80	5.0	8	186	30	10	10.20
03246 3	PZ2	100	6.0	10	213	36	10	14.60
03247 0	PZ3	150	8.0	13	271	41	10	20.70