


# C247



- End Mill
- Schafffräser
- Vingerfrezzen
- Fraises de finition
- Fresas de acabado
- Fresa de Acabamento



## C247



- 1.1 1.2 1.3 4.1 5.1 6.1 6.2 6.3
- 1.4 2.1 3.1 3.2 3.3 3.4 4.2 5.2 7.1 7.2 7.3 8.1

d <sub>1</sub> Ø mm	d <sub>2</sub> Ø mm	l <sub>2</sub> mm	l <sub>1</sub> mm	z e-Code	d <sub>1</sub> Ø mm	d <sub>2</sub> Ø mm	l <sub>2</sub> mm	l <sub>1</sub> mm	z e-Code
2.00	6	7	51	4 C2472.0	14.00	12	26	83	4 C24714.0
2.50	6	8	52	4 C2472.5	15.00	12	26	83	4 C24715.0
3.00	6	8	52	4 C2473.0	16.00	16	32	92	4 C24716.0
3.50	6	10	54	4 C2473.5	17.00	16	32	92	4 C24717.0
4.00	6	11	55	4 C2474.0	18.00	16	32	92	4 C24718.0
4.50	6	11	55	4 C2474.5	19.00	16	32	92	4 C24719.0
5.00	6	13	57	4 C2475.0	20.00	20	38	104	4 C24720.0
5.50	6	13	57	4 C2475.5	21.00	20	38	104	4 C24721.0
6.00	6	13	57	4 C2476.0	22.00	20	38	104	5 C24722.0
6.50	10	16	66	4 C2476.5	23.00	20	38	104	5 C24723.0
7.00	10	16	66	4 C2477.0	24.00	25	45	121	5 C24724.0
7.50	10	16	66	4 C2477.5	25.00	25	45	121	5 C24725.0
8.00	10	19	69	4 C2478.0	26.00	25	45	121	6 C24726.0
8.50	10	19	69	4 C2478.5	28.00	25	45	121	6 C24728.0
9.00	10	19	69	4 C2479.0	30.00	25	45	121	6 C24730.0
9.50	10	19	69	4 C2479.5	32.00	32	53	133	6 C24732.0
10.00	10	22	72	4 C24710.0	36.00	32	53	133	6 C24736.0 <sup>1)</sup>
11.00	12	22	79	4 C24711.0	40.00	40	63	155	6 C24740.0 <sup>1)</sup>
12.00	12	26	83	4 C24712.0					
13.00	12	26	83	4 C24713.0					

<sup>1)</sup> No centre cutting / kein Zentrumschnitt / Niet centrumsnijdend / Pas de coupe au centre / Sin corte al centro / Sem corte central