

Panasonic ideas for life

SAFETY INTERLOCK SWITCH CONSTRUCTED WITH DUAL RESTORATION SPRINGS

AV1 (GW) SWITCHES



FEATURES

- 8mm or more is assured as insulation distance between contacts (Snap-in mounting 2 Form A and 3 Form A type)
- Durability of 100,000 times (10.1A 250V AC) is assured for UL interlock circuit
- Constructed with easy-to-connect terminals

Terminal specifications is .250 Quick-Connect (based on DIN standards) Connection can be made with insulating sleeve on connecting lug

• UL/C-UL, ENEC (VDE) approved

TYPICAL APPLICATIONS

- 1. Office equipment
- Copiers
- Facsimiles
- Projectors
- 2. Home appliances
- Microwave ovens
- Refrigerators

RoHS compliant

ORDERING INFORMATION

	Ex. AV1 4 6 5 3 F						
Type of switch	Contact arrangement	Mounting method	Agency standard	Contact			
AV1: GW switch	1: 3 Form A (contact gap: 8 mm) 2: 2 Form A (contact gap: 8 mm) 3: 2 Form A (contact gap: 6 mm) 4: 1 Form A 1 Form B 5: 1 Form B 6: 1 Form A	6: Screw mounting (10.1 A) 7: Snap-in mounting type (10.1 A) 8: Snap-in mounting type with button guard (10.1 A)	3: UL/C-UL, ENEC/VDE (10.1 A 250 V AC 1 × 10 ⁵)	F: Cadmium free			

PRODUCT TYPES

	Part number				
Mounting method Button guard Contact arrangement			Contact gap mm	Part number	
	Without	1 Form A	Min. 6	AV16653F	
Screw mounting		1 Form B	Min. 3	AV15653F	
		1 Form A 1 Form B	Max. 3	AV14653F	
		2 Form A	Min. 6	AV13653F	
Snap-in mounting	Without	2 Form A	Min. 8	AV12753F	
		3 Form A	Min. 8	AV11753F	
	VAC-11-	2 Form A	Min. 8	AV12853F	
	With	3 Form A	Min. 8	AV11853F	

SPECIFICATIONS

1. Contact rating

No. of load	Resistive load ($\cos \phi = 1$)	VDE motor load ($\cos \phi = 0.6$)
125V AC	10.1A	3A
250V AC	10.1A	3A

^{*} The VDE motor load rating is in accordance with VDE 0630 motorload rating which designates an inrush current switching capability of 6 times the indicating rating.

2. Characteristics

Mechanical (at 60 cpm)		106	
Expected life	Electrical (at 20 cpm, operating speed: 10mm/sec.)	10 ⁵ (10.1A 250V AC) 5 × 10 ⁴ (10(3)A 250V~)	
Insulation resi	,	Min. 100MΩ at 500V DC	
	Between terminals	2,000 Vrms for 1 min.	
	Between terminals and other exposed metal parts	2,500 Vrms for 1 min.	
	Between terminals and ground	2,000 Vrms for 1 min.	
	resistance, max. op at 1A 6 to 8V DC)	Max. 100mΩ	
Temperature rise		Initial 45 deg. Max., After test 55 deg. Max.	
Vibration resistance		10 to 55Hz at double amplitude of 1.5mm (Contact opening Max. 1 msec.)	
Shock resistance		Min. 294 m/s ²	
Actuator strength		49 N for 1 minute	
Tensile terminal strength		Min. 147 N	
Min. operating speed		10 to 300mm/sec.	
Max. operatino	g cycle rate	60 cpm	
Temperature r	resistance	-40°C to -45°C: 48 hours, +80°C to +90°C: 48 hours	
Ambient temperature		−25 to +85°C (Not freezing below 0°C)	
Flame retardancy		UL 94V-1	
Tracking resist	tance (CTI)	Min. 175	
Contact material		AgCuO alloy	

^{*}Remark:Test condition and judgement are complying with "NECA C4505", "EN61058" and "UL1054".

3. Operating characteristics

1) Screw mounting type


Contact arrangement	Max. O.F.	Max. T.F. pushbutton position: 10mm	Max. F.P.	O.P.	Min. T.T.P.	Min. O.T.
1 Form A	(N.O. contact to ON) 4.90N	6.37N	16.6mm	(N.O. contact to ON) 12.7±0.4mm	10mm	2.1mm
1 Form B	(N.C. contact to OFF) 2.94N	7.35N	15.3mm	(N.C. contact to OFF) 14.9±0.4mm	10mm	4.3mm
1 Form A 1 Form B	(N.O. contact to ON) 5.88N	7.35N	15.3mm	(N.O. contact to ON) 12.7±0.4mm	10mm	2.1mm
1 Form A 1 Form B	(N.C. contact to OFF) 2.94N	7.35N	15.3mm	(N.C. contact to OFF) 14.9±0.4mm	10mm	2.1mm
2 Form A	(N.O. contact to ON) 7.85N	9.81N	16.6mm	(N.O. contact to ON) 12.7±0.4mm	10mm	2.1mm

2) Snap-in mounting type


Contact arrangement	Max. O.F.	Max. T.F. pushbutton position: 10mm	Max. F.P.	O.P.	Min. T.T.P.	Min. O.T.
2 Form A	(N.O. contact to ON) 7.85N	9.81N	14mm	(N.O. contact to ON) 9.3±0.4mm	7.5mm	2.1mm
3 Form A	(N.O. contact to ON) 9.81N	14.7N	14mm	(N.O. contact to ON) 9.3±0.4mm	7.5mm	2.1mm

CONSTRUCTION

[Screw mounting type (1 Form A 1 Form B)




[Snap-in mounting type (3 Form A)



CONTACT OPERATION CHART

- 1 Form A
- 1. Free position
- 2. Operating position
- 3. Total travel position



DIMENSIONS

The CAD data of the products with a CAD Data mark can be downloaded from: http://industrial.panasonic.com/ac/e


1. Screw mounting type

mm General tolerance: ±0.1

1 Form A, 1 Form B, 1 Form A 1 Form B

CAD Data





Contact gap

1 Form A: Min. 6mm 1 Form B: Min. 3mm


1 Form A 1 Form B: Max. 3mm

Remarks: Terminal no. 3 & 4 are for 1 Form A Terminal no. 1 & 2 are for 1 Form B.

2 Form A CAD Data




Contact gap 2 Form A: Min. 6mm




2. Snap-in mounting type


2 Form A CAD Data








2 Form A type with button guard



Recommended panel opening dimensions (common)




Panel thickness	1.0	2.5
Dimension A	36.7	37.7


250 Q.C.

1/1.

-14.8→



Recommended panel opening dimensions (common)



Panel thickness	1.0	2.5
Dimension A	47.0	47.3

NOTES


Contact gap 3 Form A: Min. 8mm

1. Switch mounting


Mount the switch to a smooth surface using M4 screws. Tighten the screws with 0.3 to 0.5 N·m {3 to 5 kg·cm} torque. To prevent loosening of the mounting screws, it is recommended that spring washers be used in combination with adhesive material for locking the screws.

2. Adjustment of the operating device:

With respect to the position of the operating device and the switch body, set the position as indicated in the condition on the right. If this condition is exceeded, the mechanical and electrical performance will be impaired. In addition, the force applied by the operating device should be in a perpendicular direction. Even if the pushbutton is used in the full total travel position, there will be no influence on the life of the switch. Screw mounting type



Snap-in mounting type



-14.8→

3. Confirming insulating distance:

Before mounting and wiring, the insulating distance between terminals and between terminals and ground should be checked for assurance of proper distance. With respect to the terminal connections, it is recommended that receptacles with insulating sleeves

Also, consideration should be given to the wiring not to apply force to the terminal section normally.

4. Avoid using AV1 switches in the following conditions:

- · Locations where hydrogen sulfide gas or other corrosive gases exist.
- · Locations where gasoline, thinner, or other inflammable or explosive gases exist.
- · Locations where there is dust and
- For operation where the perpendicular operating speed is less than 10mm/sec.
- For operation frequency of make/break exceeding 60 cpm.
- · For ambient temperatures exceeding the range of -25°C to +85°C.
- For ambient humidity exceeding 85% R.H.
- For use in a silicon atmosphere.

5. For use of AV14653F (1a1b type):

For the type AV14653F, the air distance between the N.O. and N.C. contacts is less than the required value of VDE. The N.O. and the N.C. contacts can carry only the same electric potential.