



### Main

Range of product	IC60
Device short name	Vigi iC60
Poles description	4P
Network type	AC

### Complementary

[In] rated current	25 A
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V EN 61009-1 AC 50/60 Hz 400/415 V IEC 61009-1 AC 50/60 Hz
Overvoltage protection	Without
Residual current tripping technology	Voltage independent
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
Local signalling	Trip indicator
Mounting mode	Removable comb busbar installed
Mounting support	DIN rail
Electrical connection to mcb	Plug in
9 mm pitches	6
Width	54 mm
Colour	White
Connections - terminals	Tunnel terminal with flap downside

### Environment

Standards	EN 61009-1 IEC 61009-1
-----------	---------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.