



Main

Range of product	Multi 9
Modular device name	IC2000
Modular device type	Light sensitive switch
Modular device additional info	Cabling test function with a pushbutton on front face Supplied with wall-mounted cell

Complementary

Bulb type	230 V AC halogen lamp 2300 W 230 V AC incandescent lamp 2300 W Dual mounted fluorescent tube conventional 2300 VA Dual mounted fluorescent tube electronic 300 VA Fluocompact lamp conventional 1500 VA Fluocompact lamp electronic 9 7 W Fluocompact lamp electronic 7 11 W Fluocompact lamp electronic 7 15 W Fluocompact lamp electronic 7 20 W Fluocompact lamp electronic 7 23 W Non-corrected fluorescent tube conventional 2300 VA Non-corrected mercury and sodium vapour lamps 1000 VA Parallel-corrected fluorescent tube conventional 400 VA Parallel-corrected mercury and sodium vapour lamps 400 VA Serial-corrected fluorescent tube conventional 2300 VA Serial-corrected mercury and sodium vapour lamps 1000 VA
Power consumption	6 VA
Maximum switching current	10 A 250 V AC 0.6 16 A 250 V AC 1
[Ue] rated operational voltage	230 V +10 % -15 % AC 50/60 Hz
Opening distance	< 3 mm
Status LED	LED red brightness less than the threshold LED green threshold reached
Time delay	60 s on closing 60 s on contact breaking
Product mounting	DIN rail
9 mm pitches	5
Light intensity adjustment	2...2000 lux
Connections - terminals	Screwless terminals $2 \leq 2.5 \text{ mm}^2$
Electrical insulation class	Class II
Height	11 mm
Width	9 mm
Depth	9 mm
Product weight	0.296 kg

Environment

Standards	EN 60529 EN 60669
Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP20 B