



SITOP BATTERY MODULE 24 V/3.2 AH
 SITOP BATTERY MODULE 24 V/3.2 AH WITH SERVICE-FREE
 SEALED LEAD-ACID BATTERIES FOR SITOP DC UPS MODULE 6
 A AND 15 A

Charging current charging voltage

End-of-charge voltage for DC	
<ul style="list-style-type: none"> • at 10 °C recommended • at 20 °C recommended • at 30 °C recommended • at 40 °C recommended • at 50 °C recommended 	<p>27.8 V</p> <p>27.3 V</p> <p>26.8 V</p> <p>26.6 V</p> <p>26.3 V</p>
Permissible charging current, max.	0.8 A

Safety

Short-circuit protection	Battery fuse 15 A/32 V (solid-state circuitry blade-type fuse + support)
Design of the overload protection	Valve control

Safety

Protection class	Class III
CE mark	Yes
UL/cUL (CSA) approval	cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
Degree of protection (EN 60529)	IP00

Operating data note

Operating data note	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
Ambient temperature	

<ul style="list-style-type: none"> • during operation 	-15 ... +50 °C
<ul style="list-style-type: none"> • during transport 	-20 ... +50 °C
<ul style="list-style-type: none"> • during storage 	-20 ... +50 °C
Relative temporary capacity loss at 20 °C in a month typical	3 %

Service life

Service life of lead-acid battery	
<ul style="list-style-type: none"> • typical Note 	capacity falls to 50 % of original capacity
<ul style="list-style-type: none"> • at 20 °C typical 	4 y
<ul style="list-style-type: none"> • at 30 °C typical 	2 y
<ul style="list-style-type: none"> • at 40 °C typical 	1 y
<ul style="list-style-type: none"> • at 50 °C typical 	0.5 y
Ambient temperature during storage Note	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.

Mechanics

Connection technology	spring-loaded terminals
Connection for power supply unit	1 screw terminal each for 0.08 ... 2.5 mm ² for + BATT and - BATT
Product component belonging to	Accessories pack with solid-state circuitry fuse 15 A
Width of the enclosure	190 mm
Height of the enclosure	151 mm
Depth of the enclosure	82 mm
Installation width	210 mm
Installation height	171 mm
Weight, approx.	3.2 kg
Installation	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws
Number of cells	12
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)